







POWERHOUSE™ TIMING PULLEYS

(Compatible with PowerGrip® GT2® and PowerGrip® GT3® pitches)

14 mm Pitch
For 55 mm Wide Belts
Iron
Black Oxide Plating
Taper-Lock® Style



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bushing	Face Width (in)	Overall Length (in)
28-14P55-2012	28	A1F	4.912	4.802	5.562	2012	2.750	2.750
29-14P55-2012	29	A1F	5.088	4.978	5.562	2012	2.750	2.750
30-14P55-2517	30	A1F	5.263	5.153	5.763	2517	2.750	2.750
32-14P55-2517	32	A1F	5.614	5.504	6.124	2517	2.750	2.750
34-14P55-2517	34	A1F	5.965	5.855	6.465	2517	2.750	2.750
36-14P55-2517	36	A1F	6.316	6.206	6.816	2517	2.750	2.750
38-14P55-2517	38	A1F	6.669	6.559	7.167	2517	2.750	2.750
40-14P55-2517	40	A1F	7.018	6.908	7.518	2517	2.750	2.750
44-14P55-2517	44	A1F	7.720	7.610	8.395	2517	2.750	2.750
48-14P55-3020	48	A1F	8.421	8.311	8.941	3020	2.750	2.750
52-14P55-3020	52	A1F	9.123	9.013	9.687	3020	2.750	2.750
56-14P55-3020	56	A1F	9.825	9.715	10.355	3020	2.750	2.750
60-14P55-3020	60	A1F	10.527	10.417	11.067	3020	2.750	2.750
64-14P55-3020	64	A1F	11.229	11.119	11.750	3020	2.750	2.750
68-14P55-3020	68	D1F	11.930	11.820	12.500	3020	2.750	2.750
72-14P55-3020	72	D1F	12.632	12.522	13.187	3020	2.750	2.750
80-14P55-3020	80	D3F	14.036	13.926	14.625	3020	2.750	2.750
90-14P55-3020	90	D3	15.790	15.680	-	3020	2.750	2.750
112-14P55-3020	112	D2	19.650	19.540	-	3020	2.750	2.750
144-14P55-3020	144	D3	25.264	25.154	-	3020	2.750	2.750
168-14P55-3020	168	D3	29.475	29.365	-	3020	2.750	2.750
192-14P55-3535	192	C3	33.686	33.576	-	3535	2.750	3.500



B&B Manufacturing offers an online, interactive competitor's part number cross reference tool on our website at www.bbman.com.

This powerful cross reference tool is intended to be used to determine an equivalent B&B Manufacturing part number given another manufacturer's part number. Most major precision mechanical component and power transmission manufacturers and distributors are included in this utility.