


T2.5 TIMING PULLEY BAR STOCK

METRIC TIMING PULLEY STOCK

T2.5 mm Pitch
Aluminum



Timing Pulley Stock

Part Number	No. of Teeth	Metric		Inch		Shank Diameter	Shank Length	Minimum Usable Length	Overall Length
		Pitch Diameter	Outside Diameter	Pitch Diameter	Outside Diameter				
10T2.5-PS50A	10	8.1 mm	7.4 mm	0.317"	0.293"	0.314"	1.000"	2.000"	3.000"
12T2.5-PS50A	12	9.6 mm	9.0 mm	0.378"	0.354"	0.375"	1.000"	2.000"	3.000"
13T2.5-PS50A	13	10.4 mm	9.8 mm	0.409"	0.386"	0.437"	1.000"	2.000"	3.000"
14T2.5-PS50A	14	11.2 mm	10.6 mm	0.441"	0.417"	0.437"	1.000"	2.000"	3.000"
15T2.5-PS50A	15	12.0 mm	11.4 mm	0.472"	0.449"	0.500"	1.000"	2.000"	3.000"
16T2.5-PS50A	16	12.8 mm	12.2 mm	0.504"	0.480"	0.500"	1.000"	2.000"	3.000"
17T2.5-PS50A	17	13.6 mm	13.0 mm	0.535"	0.512"	0.375"	1.000"	2.000"	3.000"
18T2.5-PS50A	18	14.4 mm	13.8 mm	0.567"	0.543"	0.375"	1.000"	2.000"	3.000"
19T2.5-PS90A	19	15.2 mm	14.6 mm	0.598"	0.575"	0.375"	1.000"	3.500"	4.500"
20T2.5-PS90A	20	16.0 mm	15.4 mm	0.630"	0.606"	0.500"	1.000"	3.500"	4.500"
21T2.5-PS90A	21	16.8 mm	16.2 mm	0.661"	0.638"	0.500"	1.000"	3.500"	4.500"
22T2.5-PS125A	22	17.6 mm	17.0 mm	0.693"	0.669"	0.500"	1.000"	4.900"	5.900"
24T2.5-PS125A	24	19.2 mm	18.5 mm	0.754"	0.730"	0.500"	1.000"	4.900"	5.900"
25T2.5-PS125A	25	19.9 mm	19.4 mm	0.785"	0.762"	0.500"	1.000"	4.900"	5.900"
26T2.5-PS125A	26	20.8 mm	20.1 mm	0.817"	0.793"	0.500"	1.000"	4.900"	5.900"
27T2.5-PS125A	27	21.5 mm	21.0 mm	0.848"	0.825"	0.500"	1.000"	4.900"	5.900"
28T2.5-PS125A	28	22.4 mm	21.7 mm	0.880"	0.856"	0.500"	1.000"	4.900"	5.900"
29T2.5-PS125A	29	23.1 mm	22.6 mm	0.911"	0.888"	0.500"	1.000"	4.900"	5.900"
30T2.5-PS125A	30	24.0 mm	23.3 mm	0.943"	0.919"	0.500"	1.000"	4.900"	5.900"
32T2.5-PS125A	32	25.6 mm	24.9 mm	1.006"	0.982"	0.500"	1.000"	4.900"	5.900"
34T2.5-PS125A	34	27.2 mm	26.5 mm	1.069"	1.045"	0.500"	1.000"	4.900"	5.900"
35T2.5-PS132A	35	27.9 mm	27.4 mm	1.100"	1.077"	0.500"	1.000"	5.200"	6.200"
36T2.5-PS132A	36	28.8 mm	28.1 mm	1.132"	1.108"	0.500"	1.000"	5.200"	6.200"