





# POWERHOUSE™ TIMING PULLEYS

(Compatible with PowerGrip® GT2® and PowerGrip® GT3® pitches)

**8 mm Pitch**  
**For 85 mm Wide Belts**  
**Steel/Iron**  
**Black Oxide Plating**  
**Taper-Lock® Style**



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bushing	Face Width (in)	Overall Length (in)
34-8P85-1615	34	A1F	3.409	3.355	3.819	1615	3.750	3.750
36-8P85-1615	36	A1F	3.609	3.555	3.938	1615	3.750	3.750
38-8P85-1610	38	A1F	3.810	3.756	4.156	1610	3.750	3.750
40-8P85-2012	40	A1F	4.010	3.956	4.331	2012	3.750	3.750
44-8P85-2012	44	A1F	4.411	4.357	4.764	2012	3.750	3.750
48-8P85-2012	48	A1F	4.812	4.758	5.157	2012	3.750	3.750
56-8P85-2517	56	A1F	5.614	5.560	5.945	2517	3.750	3.750
64-8P85-2517	64	A1F	6.416	6.362	6.772	2517	3.750	3.750
72-8P85-3020	72	A1F	7.218	7.164	7.575	3020	3.750	3.750
80-8P85-3020	80	A1F	8.020	7.966	8.386	3020	3.750	3.750
90-8P85-3020	90	A1	9.023	8.969	-	3020	3.750	3.750
112-8P85-3020	112	D1	11.229	11.175	-	3020	3.750	3.750
144-8P85-3535	144	D1	14.437	14.383	-	3535	3.750	3.750
192-8P85-3535	192	D1	19.249	19.195	-	3535	3.750	3.750



B&B Manufacturing has invested in a new Low Temperature Black Oxide line from Birchwood Casey. This system brings a previously outsourced process into B&B Manufacturing allowing us a cost-effective solution with a quicker turn around time. This particular system named TRU TEMP® provides a finish without Salt Bleed Out on all non-Stainless Steels and Cast Iron while remaining safe, operator friendly, RoHS compliant, and with no EPA problems.