


8 MM POWERHOUSE™ HTD® TIMING PULLEY FLANGES

8 mm Pitch
Steel



Part Number	Metric				Inch			
	Inside Diameter	Outside Diameter	Stock Thickness	Overall Formed Thickness	Inside Diameter	Outside Diameter	Stock Thickness	Overall Formed Thickness
18-8M-FS	36.0 mm	52.3 mm	1.9 mm	2.5 mm	1.418"	2.060"	0.075"	0.100"
22-8M-FS	44.8 mm	65.0 mm	2.3 mm	3.2 mm	1.763"	2.559"	0.090"	0.125"
24-8M-FS	49.8 mm	70.0 mm	2.3 mm	3.2 mm	1.960"	2.756"	0.090"	0.125"
26-8M-FS	54.8 mm	75.0 mm	2.3 mm	3.2 mm	2.156"	2.953"	0.090"	0.125"
28-8M-FS	59.7 mm	80.0 mm	2.3 mm	3.2 mm	2.351"	3.150"	0.090"	0.125"
30-8M-FS	64.7 mm	85.0 mm	2.3 mm	3.2 mm	2.548"	3.346"	0.090"	0.125"
32-8M-FS	69.7 mm	90.0 mm	2.3 mm	3.2 mm	2.744"	3.543"	0.090"	0.125"
34-8M-FS	76.7 mm	97.0 mm	2.3 mm	3.2 mm	3.020"	3.819"	0.090"	0.125"
36-8M-FS	79.7 mm	100.0 mm	2.3 mm	3.2 mm	3.138"	3.938"	0.090"	0.125"
38-8M-FS	84.9 mm	105.6 mm	2.3 mm	3.2 mm	3.343"	4.156"	0.090"	0.125"
40-8M-FS	89.7 mm	110.0 mm	2.3 mm	3.2 mm	3.530"	4.331"	0.090"	0.125"
44-8M-FS	100.7 mm	121.0 mm	2.3 mm	3.2 mm	3.963"	4.764"	0.090"	0.125"
48-8M-FS	109.6 mm	131.0 mm	2.3 mm	3.2 mm	4.316"	5.157"	0.090"	0.125"
56-8M-FS	129.6 mm	151.0 mm	2.3 mm	3.2 mm	5.103"	5.945"	0.090"	0.125"
64-8M-FS	149.6 mm	172.0 mm	2.3 mm	3.2 mm	5.889"	6.772"	0.090"	0.125"
72-8M-FS	169.5 mm	192.4 mm	2.3 mm	3.2 mm	6.675"	7.575"	0.090"	0.125"
80-8M-FS	191.6 mm	213.0 mm	2.3 mm	3.2 mm	7.545"	8.386"	0.090"	0.125"

Timing Pulley Flanges



For matching 8 mm
POWERHOUSE™ HTD®
timing pulleys,
see page 110.



For matching 8 mm
POWERHOUSE™ HTD®
timing belts,
see page 238.