


H TIMING PULLEY BAR STOCK


0.500" Pitch

Aluminum



Timing Pulley Stock

Part Number	No. of Teeth	Metric		Inch		Shank Diameter	Shank Length	Minimum Usable Length	Overall Length
		Pitch Diameter	Outside Diameter	Pitch Diameter	Outside Diameter				
10H-PS10A	10	40.4 mm	39.1 mm	1.592"	1.538"	0.750"	1.000"	10.000"	11.000"
11H-PS10A	11	44.5 mm	43.1 mm	1.752"	1.698"	0.750"	1.000"	10.000"	11.000"
12H-PS10A	12	48.5 mm	47.1 mm	1.910"	1.856"	0.750"	1.000"	10.000"	11.000"
14H-PS10A	14	56.6 mm	55.2 mm	2.228"	2.174"	0.750"	1.000"	10.000"	11.000"
15H-PS10A	15	60.6 mm	59.3 mm	2.387"	2.333"	0.750"	1.000"	10.000"	11.000"
16H-PS10A	16	64.7 mm	63.3 mm	2.546"	2.492"	1.000"	1.000"	10.000"	11.000"
17H-PS10A	17	68.7 mm	67.4 mm	2.706"	2.652"	1.000"	1.000"	10.000"	11.000"
18H-PS10A	18	72.8 mm	71.4 mm	2.865"	2.811"	1.000"	1.000"	10.000"	11.000"
19H-PS10A	19	76.8 mm	75.4 mm	3.024"	2.970"	1.000"	1.000"	10.000"	11.000"
20H-PS10A	20	80.8 mm	79.5 mm	3.183"	3.129"	1.000"	1.000"	10.000"	11.000"
21H-PS10A	21	84.9 mm	83.5 mm	3.342"	3.288"	1.000"	1.000"	10.000"	11.000"
22H-PS10A	22	88.9 mm	87.6 mm	3.501"	3.447"	1.000"	1.000"	10.000"	11.000"
23H-PS10A	23	93.0 mm	91.6 mm	3.662"	3.608"	1.000"	1.000"	10.000"	11.000"
24H-PS10A	24	97.0 mm	95.7 mm	3.820"	3.766"	1.000"	1.000"	10.000"	11.000"
25H-PS10A	25	101.1 mm	99.7 mm	3.980"	3.926"	1.000"	1.000"	10.000"	11.000"
26H-PS10A	26	105.1 mm	103.7 mm	4.138"	4.084"	1.000"	1.000"	10.000"	11.000"
27H-PS10A	27	109.2 mm	107.8 mm	4.299"	4.245"	1.000"	1.000"	10.000"	11.000"
28H-PS10A	28	113.2 mm	111.8 mm	4.456"	4.402"	1.000"	1.000"	10.000"	11.000"
29H-PS10A	29	117.3 mm	115.9 mm	4.617"	4.563"	1.000"	1.000"	10.000"	11.000"



For matching H pitch belts, see page 199.



For H pitch timing pulleys, see page 48.