

T5 TIMING PULLEYS

METRIC TIMING PULLEY

5 mm Pitch

For 10 mm Wide Belts




Hub

Zinc Plated Steel Flanges


Aluminum



Part Number	No. of Teeth	Type	Pitch Dia (mm)	Out. Dia. (mm)	Flange Dia (mm)	Bore (mm)	Face Width (mm)	Overall Length (mm)	Hub Dia. (mm)
21T5/10-2	10	6F	16.1	15.1		4.0	15.0	21.0	8.0
21T5/12-2	12	6F	19.3	18.3	23.0	4.0	15.0	21.0	12.0
21T5/14-2	14	6F	22.5	21.5	25.0	4.0	15.0	21.0	14.0
21T5/15-2	15	6F	24.1	23.1	28.0	6.0	15.0	21.0	16.0
21T5/16-2	16	6F	25.6	24.6	32.0	6.0	15.0	21.0	18.0
21T5/18-2	18	6F	28.8	27.8	32.0	6.0	15.0	21.0	20.0
21T5/19-2	19	6F	30.4	29.4	36.0	6.0	15.0	21.0	22.0
21T5/20-2	20	6F	32.0	31.0	36.0	6.0	15.0	21.0	24.0
21T5/22-2	22	6F	35.3	34.3	38.0	6.0	15.0	21.0	25.0
21T5/24-2	24	6F	38.4	37.4	42.0	6.0	15.0	21.0	26.0
21T5/25-2	25	6F	40.0	39.0	44.0	6.0	15.0	21.0	26.0
21T5/26-2	26	6F	41.6	40.6	44.0	6.0	15.0	21.0	26.0
21T5/27-2	27	6F	43.2	42.2	48.0	8.0	15.0	21.0	30.0
21T5/30-2	30	6F	47.8	47.0	51.0	8.0	15.0	21.0	34.0
21T5/32-2	32	6F	50.9	50.1	54.0	8.0	15.0	21.0	38.0
21T5/36-2	36	6F	57.3	56.5	63.0	8.0	15.0	21.0	38.0
21T5/40-2	40	6F	63.7	62.9	66.0	8.0	15.0	21.0	40.0
21T5/48-0	48	6	76.4	75.6	-	8.0	15.0	21.0	50.0
21T5/60-0	60	6	95.5	94.7	-	8.0	15.0	21.0	65.0



For T5 pitch pulley stock, see page 331.



For matching T5 pitch belts, see page 206.

The T5 pitch is a metric pitch tooth profile and is trapezoidal in shape. T5 pitch pulley part numbers can tell you a great deal about the pulley including the number of teeth, pitch, overall length, and number of flanges.

For more information on part numbers and their meaning, see page 441.