



8 MM POWERHOUSE™ HTD® TIMING PULLEY FLANGES

8 mm Pitch
Aluminum



Timing Pulley Flanges

Part Number	Metric				Inch			
	Inside Diameter	Outside Diameter	Stock Thickness	Overall Formed Thickness	Inside Diameter	Outside Diameter	Stock Thickness	Overall Formed Thickness
22-8M-FA	44.8 mm	65.0 mm	2.3 mm	3.2 mm	1.763"	2.559"	0.090"	0.125"
24-8M-FA	49.8 mm	70.0 mm	2.3 mm	3.2 mm	1.960"	2.756"	0.090"	0.125"
26-8M-FA	54.8 mm	75.0 mm	2.3 mm	3.2 mm	2.156"	2.953"	0.090"	0.125"
28-8M-FA	59.7 mm	80.0 mm	2.3 mm	3.2 mm	2.351"	3.150"	0.090"	0.125"
30-8M-FA	64.7 mm	85.0 mm	2.3 mm	3.2 mm	2.548"	3.346"	0.090"	0.125"
32-8M-FA	69.7 mm	90.0 mm	2.3 mm	3.2 mm	2.744"	3.543"	0.090"	0.125"
34-8M-FA	76.7 mm	97.0 mm	2.3 mm	3.2 mm	3.020"	3.819"	0.090"	0.125"
36-8M-FA	79.7 mm	100.0 mm	2.3 mm	3.2 mm	3.138"	3.938"	0.090"	0.125"
38-8M-FA	84.9 mm	105.6 mm	2.3 mm	3.2 mm	3.343"	4.156"	0.090"	0.125"
40-8M-FA	89.7 mm	110.0 mm	2.3 mm	3.2 mm	3.530"	4.331"	0.090"	0.125"
44-8M-FA	100.7 mm	121.0 mm	2.3 mm	3.2 mm	3.963"	4.764"	0.090"	0.125"
56-8M-FA	129.6 mm	151.0 mm	2.3 mm	3.2 mm	5.103"	5.945"	0.090"	0.125"
64-8M-FA	149.6 mm	172.0 mm	2.3 mm	3.2 mm	5.889"	6.772"	0.090"	0.125"
72-8M-FA	169.5 mm	193.0 mm	2.3 mm	3.2 mm	6.675"	7.598"	0.090"	0.125"
80-8M-FA	187.5 mm	213.0 mm	2.3 mm	3.2 mm	7.382"	8.386"	0.090"	0.125"



B&B Manufacturing is equipped to hob pulleys, gears, and sprockets in a large variety of tooth profiles from a large variety of materials. The possibilities are virtually endless with our state-of-the-art machining capabilities. B&B Manufacturing's Custom Shop can handle virtually all precision mechanical component requests.

B&B Manufacturing offers an online, interactive competitor's part number cross reference tool on our website.

This powerful cross reference tool is intended to be used to determine an equivalent B&B Manufacturing part number given another manufacturer's part number. Most major precision mechanical component and power transmission manufacturers and distributors are included in this utility.

For this and other useful tools, visit our website at:

www.bbman.com.