

# POWERHOUSE MX™ TIMING PULLEYS

(Compatible with Poly Chain® GT® Carbon belts)

8 mm Pitch

For 62 mm Wide Belts

Steel/Iron

Black Oxide Plating



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bore/Bushing	Face Width (in)	Overall Length (in)
22-8MX62-6FS10	22	6F	2.206	2.143	2.559	1.000	2.906	3.563
25-8MX62-6FS10	25	6F	2.506	2.443	2.953	1.000	2.906	3.563
28-8MX62-6FS10	28	6F	2.807	2.744	3.150	1.000	2.906	3.563
30-8MX62-6FS10	30	6F	3.008	2.945	3.346	1.000	2.906	3.500
32-8MX62-6FS10	32	6F	3.208	3.145	3.543	1.000	2.906	3.500
34-8MX62-1610	34	A1F	3.409	3.346	3.819	1610	2.906	2.906
34-8MX62-6FS10	34	6F	3.409	3.346	3.819	1.000	2.906	3.500
36-8MX62-1610	36	A1F	3.609	3.546	3.938	1610	2.906	2.906
36-8MX62-6FS10	36	6F	3.609	3.546	3.938	1.000	2.906	3.563
38-8MX62-1610	38	A1F	3.810	3.747	4.156	1610	2.906	2.906
38-8MX62-6FS10	38	6F	3.810	3.747	4.156	1.000	2.906	3.563
40-8MX62-2012	40	A1F	4.010	3.947	4.331	2012	2.906	2.906
40-8MX62-6FS10	40	6F	4.010	3.947	4.331	1.000	2.906	3.625
42-8MX62-2012	42	A1F	4.211	4.148	4.687	2012	2.906	2.906
42-8MX62-6FS10	42	6F	4.211	4.148	4.687	1.000	2.906	3.625
45-8MX62-2012	45	A1F	4.511	4.448	5.005	2012	2.906	2.906
45-8MX62-6FS10	45	6F	4.511	4.448	5.005	1.000	2.906	3.625
48-8MX62-2517	48	A1F	4.812	4.749	5.157	2517	2.906	2.906
50-8MX62-2517	50	A1F	5.013	4.950	5.320	2517	2.906	2.906
53-8MX62-2517	53	A1F	5.314	5.251	5.625	2517	2.906	2.906
56-8MX62-2517	56	A1F	5.614	5.551	5.945	2517	2.906	2.906
60-8MX62-3020	60	A1F	6.015	5.952	6.375	3020	2.906	2.906
63-8MX62-3020	63	A1F	6.316	6.253	6.772	3020	2.906	2.906
67-8MX62-3020	67	A1F	6.717	6.654	7.231	3020	2.906	2.906
71-8MX62-3020	71	A1F	7.118	7.055	7.575	3020	2.906	2.906
75-8MX62-3020	75	A1F	7.519	7.456	7.867	3020	2.906	2.906
80-8MX62-3020	80	A1F	8.020	7.957	8.386	3020	2.906	2.906
90-8MX62-3020	90	D1	9.023	8.960	-	3020	2.906	2.906
112-8MX62-3020	112	D2	11.229	11.166	-	3020	2.906	2.906
140-8MX62-3525	140	D2	14.036	13.973	-	3525	2.906	2.906
180-8MX62-3525	180	D3	18.046	17.983	-	3525	2.906	2.906
224-8MX62-3525	224	D3	22.457	22.394	-	3525	2.906	2.906

