

H TIMING PULLEYS

0.500" Trapezoidal Pitch

For 1" Wide Belts

Hub and Flanges



Steel/Iron

Black Oxide Plating


Minimum Plain Bore



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bore (in)	Face Width (in)	Overall Length (in)
14H100-6FS7	14	6F	2.228	2.174	2.461	0.625	1.312	1.875
16H100-6FS7	16	6F	2.546	2.492	2.780	0.625	1.312	2.000
17H100-6FS7	17	6F	2.706	2.652	3.000	0.625	1.312	2.000
18H100-6FS7	18	6F	2.865	2.811	3.100	0.625	1.312	2.000
19H100-6FS7	19	6F	3.024	2.970	3.256	0.625	1.312	2.000
20H100-6FS7	20	6F	3.183	3.129	3.420	0.625	1.312	2.125
21H100-6FS8	21	6F	3.342	3.288	3.574	0.750	1.312	2.125
22H100-6FS8	22	6F	3.501	3.447	3.735	0.750	1.312	2.250
24H100-6FS8	24	6F	3.820	3.766	4.050	0.750	1.312	2.250
26H100-6FS8	26	6F	4.138	4.084	4.369	0.750	1.312	2.375
28H100-6FS8	28	6F	4.456	4.402	4.687	0.750	1.312	2.375
30H100-6FS8	30	6F	4.775	4.721	5.005	0.750	1.312	2.375



For matching L pitch belts, see page 194.



For H pitch pulley stock and flanges, see page 199.



For the latest information on B&B Manufacturing including inclement weather closings, career opportunities, and our holiday schedule, follow us on Facebook at www.facebook.com/bandbmanufacturing.