


TAPER-LOCK® BUSHINGS

Steel/Iron




1008 thru 3030 Sizes

BORE	KEYWAY
0.500" - 0.563"	0.125" X 0.630"
0.625" - 0.875"	0.188" X 0.938"
0.938" - 1.250"	0.250" X 0.125"
1.438" - 1.750"	0.375" X 0.188"
1.813" - 2.250"	0.500" X 0.250"
2.313" - 2.750"	0.625" X 0.313"
2.813" - 3.250"	0.750" X 0.375"
3.313" - 3.750"	0.875" X 0.438"
3.813" - 4.500"	1.000" X 0.500"



3535 thru 5050 Sizes



Bushing	Bore Range	Dimensions					Torque Capacity In-Lbs
		A	B	C	D	G	
1008	0.500" - 1.000"	1.375"	0.875"	2.188"	1.328"	-	1,200
1108	0.500" - 1.125"	1.500"	0.875"	2.313"	1.453"	-	1,300
1210	0.500" - 1.250"	1.875"	1.000"	3.250"	1.750"	-	3,600
1215	0.500" - 1.250"	1.875"	1.500"	2.875"	1.750"	-	3,550
1310	0.500" - 1.375"	2.000"	1.000"	3.375"	1.875"	-	3,850
1610	0.500" - 1.625"	2.250"	1.000"	3.625"	2.125"	-	4,300
1615	0.500" - 1.625"	2.250"	1.500"	3.250"	2.125"	-	4,300
2012	0.500" - 2.000"	2.750"	1.250"	4.375"	2.625"	-	7,150
2517	0.500" - 2.500"	3.375"	1.750"	4.875"	3.250"	-	11,600
2525	0.750" - 2.500"	3.375"	2.500"	4.500"	3.250"	-	11,300
3020	0.938" - 3.000"	4.250"	2.000"	6.250"	4.000"	-	24,000
3030	0.938" - 3.000"	4.250"	3.000"	5.750"	4.000"	-	24,000
3525	1.188" - 3.938"	5.000"	2.500"	7.000"	4.830"	39	44,800
3535	1.188" - 3.500"	5.000"	3.500"	7.000"	4.830"	39	44,800
4030	1.438" - 4.438"	5.750"	3.000"	8.500"	5.540"	39	77,300
4040	1.438" - 4.000"	5.750"	4.000"	8.500"	5.540"	40	77,300
4535	1.938" - 4.938"	6.375"	3.500"	9.500"	6.125"	40	110,000
4545	2.313" - 4.938"	6.375"	4.500"	9.500"	6.125"	40	110,000
5040	2.438" - 5.000"	7.000"	4.000"	10.500"	6.720"	37	126,000
5050	2.438" - 5.000"	7.000"	5.000"	10.500"	6.720"	37	126,000