


# 5 MM POWERHOUSE™ TIMING PULLEY FLANGES


(Compatible with PowerGrip® GT2® and PowerGrip® GT3® pitches)

**5 mm Pitch  
Aluminum**




| Part Number | Metric          |                  |                 |                          | Inch            |                  |                 |                          |
|-------------|-----------------|------------------|-----------------|--------------------------|-----------------|------------------|-----------------|--------------------------|
|             | Inside Diameter | Outside Diameter | Stock Thickness | Overall Formed Thickness | Inside Diameter | Outside Diameter | Stock Thickness | Overall Formed Thickness |
| 12-5P-FA    | 12.8 mm         | 22.2 mm          | 1.0 mm          | 1.7 mm                   | 0.503"          | 0.875"           | 0.040"          | 0.065"                   |
| 13-5P-FA    | 14.3 mm         | 23.8 mm          | 1.0 mm          | 1.7 mm                   | 0.562"          | 0.937"           | 0.040"          | 0.065"                   |
| 14-5P-FA    | 14.3 mm         | 25.4 mm          | 1.0 mm          | 1.7 mm                   | 0.562"          | 1.000"           | 0.040"          | 0.065"                   |
| 15-5P-FA    | 15.9 mm         | 27.0 mm          | 1.0 mm          | 1.7 mm                   | 0.625"          | 1.062"           | 0.040"          | 0.065"                   |
| 16-5P-FA    | 17.4 mm         | 27.8 mm          | 1.0 mm          | 1.7 mm                   | 0.684"          | 1.093"           | 0.040"          | 0.065"                   |
| 17-5P-FA    | 19.0 mm         | 30.1 mm          | 1.0 mm          | 1.7 mm                   | 0.748"          | 1.187"           | 0.040"          | 0.065"                   |
| 18-5P-FA    | 20.6 mm         | 31.8 mm          | 1.0 mm          | 1.7 mm                   | 0.810"          | 1.250"           | 0.040"          | 0.065"                   |
| 19-5P-FA    | 22.5 mm         | 33.3 mm          | 1.0 mm          | 1.7 mm                   | 0.887"          | 1.312"           | 0.040"          | 0.065"                   |
| 20-5P-FA    | 23.8 mm         | 34.9 mm          | 1.0 mm          | 1.7 mm                   | 0.936"          | 1.375"           | 0.040"          | 0.065"                   |
| 21-5P-FA    | 25.4 mm         | 36.5 mm          | 1.0 mm          | 1.7 mm                   | 1.000"          | 1.437"           | 0.040"          | 0.065"                   |
| 22-5P-FA    | 27.0 mm         | 38.1 mm          | 1.0 mm          | 1.7 mm                   | 1.062"          | 1.500"           | 0.040"          | 0.065"                   |
| 23-5P-FA    | 28.6 mm         | 39.7 mm          | 1.0 mm          | 1.7 mm                   | 1.125"          | 1.562"           | 0.040"          | 0.065"                   |
| 24-5P-FA    | 29.5 mm         | 41.3 mm          | 1.0 mm          | 1.7 mm                   | 1.160"          | 1.625"           | 0.040"          | 0.065"                   |
| 25-5P-FA    | 31.0 mm         | 42.8 mm          | 1.0 mm          | 1.7 mm                   | 1.222"          | 1.687"           | 0.040"          | 0.065"                   |
| 26-5P-FA    | 31.0 mm         | 44.5 mm          | 1.0 mm          | 1.7 mm                   | 1.222"          | 1.750"           | 0.040"          | 0.065"                   |
| 28-5P-FA    | 34.2 mm         | 47.6 mm          | 1.0 mm          | 1.7 mm                   | 1.347"          | 1.875"           | 0.040"          | 0.065"                   |
| 30-5P-FA    | 36.2 mm         | 50.8 mm          | 1.0 mm          | 1.7 mm                   | 1.425"          | 2.000"           | 0.040"          | 0.065"                   |
| 32-5P-FA    | 39.4 mm         | 54.0 mm          | 1.0 mm          | 1.7 mm                   | 1.550"          | 2.125"           | 0.040"          | 0.065"                   |
| 34-5P-FA    | 42.5 mm         | 57.2 mm          | 1.0 mm          | 1.7 mm                   | 1.675"          | 2.250"           | 0.040"          | 0.065"                   |

Timing Pulley Flanges



For matching 5 mm  
POWERHOUSE™ pitch  
timing pulleys,  
see page 135.



For matching 5 mm  
POWERHOUSE™ pitch  
timing belts,  
see page 237.