

5V V-BELT SHEAVES

For 5V V-Belts

2 Grooves

1.688" Face Width


Cast Iron

QD® Style




Part Number	Bushing	Bore Range	Type	Pitch Dia. "5V" Belts (in)	Out. Dia. (in)	E	L	M	Wt. Ea. (Lbs.)
25V440SH	SH	0.500" - 1.625"	D1	4.30	4.40	0.344	1.313	0.719	5.8
25V465SDS	SDS	0.500" - 2.000"	E1	4.55	4.65	0.844	1.313	0.469	6.6
25V490SDS	SDS	0.500" - 2.000"	A1	4.80	4.90	0.031	1.313	0.344	6.8
25V520SDS	SDS	0.500" - 2.000"	A1	5.10	5.20	0.031	1.313	0.344	7.0
25V550SDS	SDS	0.500" - 2.000"	A1	5.40	5.50	0.031	1.313	0.344	7.2
25V590SDS	SDS	0.500" - 2.000"	A1	5.80	5.90	0.031	1.313	0.344	7.6
25V630SK	SK	0.500" - 2.625"	D1	6.20	6.30	0.344	1.938	0.094	9.4
25V670SK	SK	0.500" - 2.625"	D1	6.60	6.70	0.344	1.938	0.094	10.5
25V710SK	SK	0.500" - 2.625"	D1	7.00	7.10	0.344	1.938	0.094	11.5
25V750SK	SK	0.500" - 2.625"	D1	7.40	7.50	0.344	1.938	0.094	12.5
25V800SK	SK	0.500" - 2.625"	D2	7.90	8.00	0.344	1.938	0.094	13.0
25V850SK	SK	0.500" - 2.625"	D2	8.40	8.50	0.344	1.938	0.094	14.0
25V900SK	SK	0.500" - 2.625"	D3	8.90	9.00	0.344	1.938	0.094	15.2
25V925SK	SK	0.500" - 2.625"	D3	9.15	9.25	0.344	1.938	0.094	15.3
25V975SK	SK	0.500" - 2.625"	D3	9.65	9.75	0.344	1.938	0.094	15.5
25V1030SK	SK	0.500" - 2.625"	D3	10.20	10.30	0.344	1.938	0.094	15.5
25V1090SK	SK	0.500" - 2.625"	D3	10.80	10.90	0.344	1.938	0.094	16.5
25V1130SK	SK	0.500" - 2.625"	D3	11.20	11.30	0.344	1.938	0.094	17.8
25V1180SK	SK	0.500" - 2.625"	D3	11.70	11.80	0.344	1.938	0.094	19.0
25V1250SF	SF	0.500" - 2.938"	D3	12.40	12.50	0.406	2.063	0.031	21.0
25V1320SF	SF	0.500" - 2.938"	D3	13.10	13.20	0.406	2.063	0.031	22.6
25V1400SF	SF	0.500" - 2.938"	D3	13.90	14.00	0.406	2.063	0.031	25.3
25V1500SF	SF	0.500" - 2.938"	D3	14.90	15.00	0.406	2.063	0.031	27.4
25V1600SF	SF	0.500" - 2.938"	D3	15.90	16.00	0.406	2.063	0.031	29.2
25V1870SF	SF	0.500" - 2.938"	D3	18.60	18.70	0.406	2.063	0.031	36.0
25V2120SF	SF	0.500" - 2.938"	D3	21.10	21.20	0.406	2.063	0.031	43.0
25V2360E	E	0.875" - 3.500"	C3	23.50	23.60	0.906	2.375	0.156	55.0
25V2800E	E	0.875" - 3.500"	C3	27.90	28.00	0.906	2.375	0.156	67.0


TYPE A



TYPE C



TYPE D



TYPE E

