


# T5 TIMING PULLEY BAR STOCK

T5 mm Pitch  
Aluminum

METRIC TIMING PULLEY STOCK



Part Number	No. of Teeth	Metric		Inch		Shank Diameter	Shank Length	Minimum Usable Length	Overall Length
		Pitch Diameter	Outside Diameter	Pitch Diameter	Outside Diameter				
10T5-PS125A	10	16.1 mm	15.1 mm	0.632"	0.593"	0.500"	0.800"	4.900"	5.700"
11T5-PS125A	11	17.7 mm	16.7 mm	0.695"	0.656"	0.500"	0.800"	4.900"	5.700"
12T5-PS125A	12	19.3 mm	18.3 mm	0.758"	0.719"	0.500"	0.800"	4.900"	5.700"
13T5-PS125A	13	20.9 mm	19.8 mm	0.821"	0.781"	0.500"	0.800"	4.900"	5.700"
14T5-PS132A	14	22.5 mm	22.5 mm	0.884"	0.884"	0.500"	0.800"	5.200"	6.000"
15T5-PS132A	15	24.1 mm	24.1 mm	0.947"	0.947"	0.500"	0.800"	5.200"	6.000"
16T5-PS140A	16	25.6 mm	24.6 mm	1.008"	0.969"	0.500"	0.800"	5.500"	6.300"
17T5-PS140A	17	27.2 mm	26.2 mm	1.071"	1.031"	0.500"	0.800"	5.500"	6.300"
18T5-PS140A	18	28.8 mm	27.8 mm	1.134"	1.094"	0.500"	0.800"	5.500"	6.300"
19T5-PS140A	19	30.4 mm	29.4 mm	1.197"	1.157"	0.500"	0.800"	5.500"	6.300"
20T5-PS160A	20	32.0 mm	31.0 mm	1.260"	1.220"	0.500"	0.800"	6.300"	7.100"
21T5-PS160A	21	33.7 mm	32.7 mm	1.327"	1.287"	0.500"	0.800"	6.300"	7.100"
22T5-PS160A	22	35.3 mm	34.2 mm	1.388"	1.348"	0.500"	0.800"	6.300"	7.100"
23T5-PS160A	23	36.9 mm	35.8 mm	1.451"	1.411"	0.500"	0.800"	6.300"	7.100"
24T5-PS160A	24	38.4 mm	37.4 mm	1.512"	1.472"	0.500"	0.800"	6.300"	7.100"
25T5-PS160A	25	40.0 mm	39.0 mm	1.575"	1.535"	0.500"	0.800"	6.300"	7.100"
26T5-PS160A	26	41.6 mm	40.6 mm	1.638"	1.598"	0.500"	0.800"	6.300"	7.100"
27T5-PS160A	27	43.2 mm	42.2 mm	1.701"	1.661"	0.500"	0.800"	6.300"	7.100"
28T5-PS160A	28	44.8 mm	43.7 mm	1.762"	1.722"	0.500"	0.800"	6.300"	7.100"
29T5-PS160A	29	46.4 mm	45.3 mm	1.825"	1.785"	0.500"	0.800"	6.300"	7.100"
30T5-PS160A	30	48.0 mm	46.9 mm	1.888"	1.848"	0.750"	0.800"	6.300"	7.100"
32T5-PS160A	32	51.1 mm	50.1 mm	2.012"	1.972"	0.750"	0.800"	6.300"	7.100"
34T5-PS160A	34	54.3 mm	53.2 mm	2.136"	2.096"	0.750"	0.800"	6.300"	7.100"

Timing Pulley Stock