


T10/AT10 TIMING PULLEY FLANGES

METRIC TIMING PULLEY FLANGE



**T10/AT10 mm Pitch
Zinc Plated Steel**

Timing Pulley Flanges

Part Number	Metric				Inch			
	Inside Diameter	Outside Diameter	Stock Thickness	Overall Formed Thickness	Inside Diameter	Outside Diameter	Stock Thickness	Overall Formed Thickness
14-T10-FS	37.0 mm	48.0 mm	1.5 mm	2.3 mm	1.457"	1.890"	0.059"	0.090"
15-T10-FS	40.0 mm	51.0 mm	1.5 mm	2.3 mm	1.516"	2.008"	0.059"	0.090"
16-T10-FS	43.0 mm	54.0 mm	1.5 mm	2.3 mm	1.693"	2.126"	0.059"	0.090"
18-T10-FS	47.0 mm	60.0 mm	1.5 mm	2.3 mm	1.890"	2.362"	0.059"	0.090"
19-T10-FS	52.0 mm	64.0 mm	1.5 mm	2.3 mm	1.850"	2.520"	0.059"	0.090"
20-T10-FS	52.0 mm	66.0 mm	1.5 mm	2.3 mm	2.047"	2.598"	0.059"	0.090"
22-T10-FS	60.0 mm	75.0 mm	1.5 mm	2.3 mm	2.244"	2.953"	0.059"	0.090"
24-T10-FS	68.0 mm	83.0 mm	1.5 mm	2.3 mm	2.677"	3.268"	0.059"	0.090"
25-T10-FS	68.0 mm	86.0 mm	1.5 mm	2.3 mm	2.677"	3.386"	0.059"	0.090"
26-T10-FS	72.0 mm	87.0 mm	1.5 mm	2.3 mm	2.835"	3.425"	0.059"	0.090"
27-T10-FS	76.0 mm	91.0 mm	1.5 mm	2.3 mm	2.874"	3.583"	0.059"	0.090"
30-T10-FS	83.0 mm	97.0 mm	1.5 mm	2.3 mm	3.110"	3.819"	0.059"	0.090"
32-T10-FS	90.0 mm	106.0 mm	1.5 mm	2.3 mm	3.386"	4.173"	0.059"	0.090"
36-T10-FS	103.0 mm	120.0 mm	1.5 mm	2.3 mm	3.917"	4.724"	0.059"	0.090"
40-T10-FS	115.0 mm	135.0 mm	1.5 mm	2.3 mm	4.528"	5.315"	0.059"	0.090"

RECOMMENDED MINIMUM FLANGE DIMENSIONS

Belt Pitch	Minimum Flange Thickness	Minimum Flange Height
MXL	0.023	0.020
XL	0.029	0.040
L	0.050	0.065
H	0.050	0.080
3 mm	0.023	0.067
5 mm	0.029	0.091
8 mm	0.078	0.168

