


8 MM POWERHOUSE™ BELTS

(Compatible with PowerGrip® GT2® and PowerGrip® GT3® pitches)

**Standard Widths:
12 mm, 20 mm, 30 mm,
50 mm, 85 mm**

**Neoprene Construction
Fiberglass Reinforcements**

(Note: Custom belt widths are available upon request.)



Timing Belts




Part Number	No. of Teeth	Pitch Length (mm)
384-8P	48	384.0
480-8P	60	480.0
560-8P	70	560.0
600-8P	75	600.0
640-8P	80	640.0
720-8P	90	720.0
800-8P	100	800.0
840-8P	105	840.0
880-8P	110	880.0
920-8P	115	920.0
960-8P	120	960.0

Part Number	No. of Teeth	Pitch Length (mm)
1040-8P	130	1040.0
1064-8P	133	1064.0
1104-8P	138	1104.0
1120-8P	140	1120.0
1160-8P	145	1160.0
1200-8P	150	1200.0
1224-8P	153	1224.0
1280-8P	160	1280.0
1440-8P	180	1440.0
1512-8P	189	1512.0
1584-8P	198	1584.0

Part Number	No. of Teeth	Pitch Length (mm)
1600-8P	200	1600.0
1760-8P	220	1760.0
1800-8P	225	1800.0
2000-8P	250	2000.0
2200-8P	275	2200.0
2400-8P	300	2400.0
2600-8P	325	2600.0
2800-8P	350	2800.0
3048-8P	381	3048.0
3280-8P	410	3280.0
3600-8P	450	3600.0
4400-8P	550	4400.0

Neoprene 8 mm POWERHOUSE™ timing belt part numbers can be determined as follows:
Pitch Length Code + -8P- + Width Code



At B&B Manufacturing, we have an extensive online catalog of timing belts that meet a wide variety of needs in the power transmission and precision mechanical marketplaces.

But we know that sometimes it takes something special to do the job right. We offer timing belts in hard to find lengths, custom widths, special materials, special reinforcements, special backings, and with high and low temperature resistances for extreme applications.