


5 MM POWERHOUSE™ HTD® TIMING PULLEY FLANGES



5 mm Pitch
Aluminum

Timing Pulley Flanges

Part Number	Metric				Inch			
	Inside Diameter	Outside Diameter	Stock Thickness	Overall Formed Thickness	Inside Diameter	Outside Diameter	Stock Thickness	Overall Formed Thickness
12-5M-FA	12.8 mm	22.2 mm	1.0 mm	1.7 mm	0.503"	0.875"	0.040"	0.065"
13-5M-FA	14.3 mm	23.8 mm	1.0 mm	1.7 mm	0.562"	0.937"	0.040"	0.065"
14-5M-FA	14.3 mm	25.4 mm	1.0 mm	1.7 mm	0.562"	1.000"	0.040"	0.065"
15-5M-FA	15.9 mm	27.0 mm	1.0 mm	1.7 mm	0.625"	1.062"	0.040"	0.065"
16-5M-FA	17.4 mm	27.8 mm	1.0 mm	1.7 mm	0.684"	1.093"	0.040"	0.065"
17-5M-FA	19.0 mm	30.1 mm	1.0 mm	1.7 mm	0.748"	1.187"	0.040"	0.065"
18-5M-FA	20.6 mm	31.8 mm	1.0 mm	1.7 mm	0.810"	1.250"	0.040"	0.065"
19-5M-FA	22.5 mm	33.3 mm	1.0 mm	1.7 mm	0.887"	1.312"	0.040"	0.065"
20-5M-FA	23.8 mm	34.9 mm	1.0 mm	1.7 mm	0.936"	1.375"	0.040"	0.065"
21-5M-FA	25.4 mm	36.5 mm	1.0 mm	1.7 mm	1.000"	1.437"	0.040"	0.065"
22-5M-FA	27.0 mm	38.1 mm	1.0 mm	1.7 mm	1.062"	1.500"	0.040"	0.065"
23-5M-FA	28.6 mm	39.7 mm	1.0 mm	1.7 mm	1.125"	1.562"	0.040"	0.065"
24-5M-FA	29.5 mm	41.3 mm	1.0 mm	1.7 mm	1.160"	1.625"	0.040"	0.065"
25-5M-FA	31.0 mm	42.8 mm	1.0 mm	1.7 mm	1.222"	1.687"	0.040"	0.065"
26-5M-FA	31.0 mm	44.5 mm	1.0 mm	1.7 mm	1.222"	1.750"	0.040"	0.065"
28-5M-FA	34.2 mm	47.6 mm	1.0 mm	1.7 mm	1.347"	1.875"	0.040"	0.065"
30-5M-FA	36.2 mm	50.8 mm	1.0 mm	1.7 mm	1.425"	2.000"	0.040"	0.065"
32-5M-FA	39.4 mm	54.0 mm	1.0 mm	1.7 mm	1.550"	2.125"	0.040"	0.065"
34-5M-FA	42.5 mm	57.2 mm	1.0 mm	1.7 mm	1.675"	2.250"	0.040"	0.065"

B&B Manufacturing is proud to be a contributing member of the Power Transmission Distributors Association, Mechanical Power Transmission Association, and the Power-Motion Technology Representatives Association. The power of these associations lies in the development of professional standards in the industry.

