



# L TIMING PULLEY FLANGES

0.375" / 9.525 mm Pitch  
Steel



Part Number	Metric				Inch			
	Inside Diameter	Outside Diameter	Stock Thickness	Overall Formed Thickness	Inside Diameter	Outside Diameter	Stock Thickness	Overall Formed Thickness
10L-FS	24.8 mm	36.5 mm	1.5 mm	2.3 mm	0.976"	1.438"	0.060"	0.090"
11L-FS	28.0 mm	38.9 mm	1.5 mm	2.3 mm	1.101"	1.531"	0.060"	0.090"
12L-FS	31.1 mm	42.1 mm	1.5 mm	2.3 mm	1.226"	1.656"	0.060"	0.090"
13L-FS	32.4 mm	45.2 mm	1.5 mm	2.3 mm	1.276"	1.781"	0.060"	0.090"
14L-FS	35.6 mm	48.4 mm	1.5 mm	2.3 mm	1.401"	1.906"	0.060"	0.090"
15L-FS	38.6 mm	51.6 mm	1.5 mm	2.3 mm	1.521"	2.031"	0.060"	0.090"
16L-FS	40.1 mm	54.0 mm	1.5 mm	2.3 mm	1.578"	2.125"	0.060"	0.090"
17L-FS	43.2 mm	57.2 mm	1.5 mm	2.3 mm	1.701"	2.250"	0.060"	0.090"
18L-FS	46.3 mm	60.3 mm	1.5 mm	2.3 mm	1.824"	2.375"	0.060"	0.090"
19L-FS	48.5 mm	63.5 mm	1.5 mm	2.3 mm	1.910"	2.500"	0.060"	0.090"
20L-FS	51.7 mm	66.7 mm	1.5 mm	2.3 mm	2.035"	2.625"	0.060"	0.090"
21L-FS	53.8 mm	69.9 mm	1.5 mm	2.3 mm	2.120"	2.750"	0.060"	0.090"
22L-FS	56.9 mm	73.0 mm	1.5 mm	2.3 mm	2.241"	2.875"	0.060"	0.090"
24L-FS	60.3 mm	78.6 mm	1.5 mm	2.3 mm	2.375"	3.094"	0.060"	0.090"
25L-FS	66.3 mm	85.7 mm	1.5 mm	2.3 mm	2.610"	3.375"	0.060"	0.090"
26L-FS	68.4 mm	84.6 mm	1.5 mm	2.3 mm	2.692"	3.330"	0.060"	0.090"
28L-FS	74.7 mm	90.6 mm	1.5 mm	2.3 mm	2.942"	3.566"	0.060"	0.090"
30L-FS	77.9 mm	96.5 mm	1.5 mm	2.3 mm	3.067"	3.800"	0.060"	0.090"
32L-FS	82.7 mm	102.7 mm	1.5 mm	2.3 mm	3.254"	4.044"	0.060"	0.090"
36L-FS	92.2 mm	114.8 mm	1.5 mm	2.3 mm	3.629"	4.520"	0.060"	0.090"
40L-FS	101.7 mm	126.9 mm	1.5 mm	2.3 mm	4.004"	4.997"	0.060"	0.090"
44L-FS	114.4 mm	139.0 mm	1.5 mm	2.3 mm	4.504"	5.474"	0.060"	0.090"
48L-FS	127.1 mm	151.1 mm	1.5 mm	2.3 mm	5.004"	5.950"	0.060"	0.090"



For matching  
L pitch belts,  
see page 194.



For L pitch  
timing pulleys,  
see page 30.