


T2.5 TIMING PULLEY FLANGES

T2.5 mm Pitch
Aluminum

METRIC TIMING PULLEY FLANGE




Part Number	Metric				Inch			
	Inside Diameter	Outside Diameter	Stock Thickness	Overall Formed Thickness	Inside Diameter	Outside Diameter	Stock Thickness	Overall Formed Thickness
14-T2.5-FA	8.2 mm	14.7 mm	0.6 mm	1.1 mm	0.322"	0.580"	0.025"	0.045"
15-T2.5-FA	8.2 mm	14.7 mm	0.6 mm	1.1 mm	0.322"	0.580"	0.025"	0.045"
16-T2.5-FA	9.5 mm	16.1 mm	0.8 mm	1.3 mm	0.374"	0.635"	0.032"	0.052"
18-T2.5-FA	10.0 mm	17.4 mm	0.8 mm	1.3 mm	0.394"	0.685"	0.032"	0.052"
19-T2.5-FA	11.5 mm	18.0 mm	0.8 mm	1.3 mm	0.452"	0.710"	0.032"	0.052"
20-T2.5-FA	12.8 mm	20.1 mm	0.8 mm	1.3 mm	0.504"	0.790"	0.032"	0.052"
22-T2.5-FA	14.6 mm	23.0 mm	0.8 mm	1.3 mm	0.575"	0.910"	0.032"	0.052"
24-T2.5-FA	14.6 mm	22.7 mm	0.8 mm	1.3 mm	0.574"	0.895"	0.032"	0.052"
25-T2.5-FA	15.9 mm	24.0 mm	0.8 mm	1.3 mm	0.626"	0.945"	0.032"	0.052"
26-T2.5-FA	17.2 mm	25.4 mm	0.8 mm	1.3 mm	0.678"	1.000"	0.032"	0.052"
28-T2.5-FA	17.2 mm	26.0 mm	0.8 mm	1.3 mm	0.677"	1.000"	0.032"	0.052"
30-T2.5-FA	21.6 mm	29.8 mm	0.8 mm	1.3 mm	0.849"	1.173"	0.032"	0.052"
32-T2.5-FA	23.5 mm	32.0 mm	1.0 mm	1.5 mm	0.926"	1.260"	0.040"	0.060"
36-T2.5-FA	26.9 mm	36.1 mm	1.0 mm	1.5 mm	1.058"	1.420"	0.040"	0.060"
40-T2.5-FA	28.2 mm	37.3 mm	1.0 mm	1.5 mm	1.110"	1.470"	0.040"	0.060"

The T2.5 pitch is a metric pitch tooth profile and is trapezoidal in shape. T2.5 pitch pulley part numbers can tell you a great deal about the pulley including the number of teeth, pitch, overall length, and number of flanges.

For more information on part numbers and their meaning, see page 441.



For matching
T2.5 pitch
timing pulleys,
see page 75.



For matching
T2.5 pitch
timing belts,
see page 205.