

T5 TIMING PULLEYS

METRIC TIMING PULLEY

5 mm Pitch

For 16 mm Wide Belts



Hub

Zinc Plated Steel Flanges

Aluminum



Part Number	No. of Teeth	Type	Pitch Dia. (mm)	Out. Dia. (mm)	Flange Dia. (mm)	Bore (mm)	Face Width (mm)	Overall Length (mm)	Hub Dia. (mm)
27T5/10-2	10	6F	16.1	15.1	19.5	4.0	21.0	27.0	8.0
27T5/12-2	12	6F	19.3	18.3	23.0	4.0	21.0	27.0	12.0
27T5/14-2	14	6F	22.5	21.5	25.0	4.0	21.0	27.0	14.0
27T5/15-2	15	6F	24.1	23.1	28.0	6.0	21.0	27.0	16.0
27T5/16-2	16	6F	25.6	24.6	32.0	6.0	21.0	27.0	18.0
27T5/18-2	18	6F	28.8	27.8	32.0	6.0	21.0	27.0	20.0
27T5/19-2	19	6F	30.4	29.4	36.0	6.0	21.0	27.0	22.0
27T5/20-2	20	6F	32.0	31.0	36.0	6.0	21.0	27.0	24.0
27T5/22-2	22	6F	35.3	34.3	38.0	6.0	21.0	27.0	25.0
27T5/24-2	24	6F	38.4	37.4	42.0	6.0	21.0	27.0	26.0
27T5/25-2	25	6F	40.0	39.0	44.0	6.0	21.0	27.0	26.0
27T5/26-2	26	6F	41.6	40.6	44.0	6.0	21.0	27.0	26.0
27T5/27-2	27	6F	43.2	42.2	48.0	8.0	21.0	27.0	30.0
27T5/30-2	30	6F	48.0	47.0	51.0	8.0	21.0	27.0	34.0
27T5/32-2	32	6F	51.1	50.1	54.0	8.0	21.0	27.0	38.0
27T5/36-2	36	6F	57.5	56.5	63.0	8.0	21.0	27.0	38.0
27T5/40-2	40	6F	63.9	62.9	66.0	8.0	21.0	27.0	40.0
27T5/48-0	48	6	76.6	75.6	-	8.0	21.0	27.0	50.0
27T5/60-0	60	6	95.7	94.7	-	8.0	21.0	27.0	65.0



Save time and money on labels by taking advantage of our custom eco-friendly marking options. Custom marking options are available with our ElectroX Laser Marking Machine, our Epilog Laser Marking Machine, and our Telesis Pin Stamp Marking Machine.