

# A-B COMBINATION V-BELT SHEAVES

For use with "A" or "B" Section Belts

2 Grooves

1.750" Face Width


Cast Iron

QD® Style




Part Number	Type	Pitch Dia. "A" belts (in)	Pitch Dia. "B" belts (in)	Out. Dia. (in)	Bushing	Bore Range	E	L	M	Wt. Ea. (Lbs.)
2B34SH	E1	3.0	3.4	3.0	SH	0.500" - 1.625"	1.094	1.313	0.656	3.2
2B36SH	D1	3.2	3.6	3.95	SH	0.500" - 1.625"	0.469	1.313	0.906	3.4
2B38SH	D1	3.4	3.8	4.15	SH	0.500" - 1.625"	1.094	1.313	0.656	3.9
2B40SH	A1	3.6	4.0	4.35	SH	0.500" - 1.625"	0.469	1.313	0.906	4.1
2B42SH	A1	3.8	4.2	4.55	SH	0.500" - 1.625"	0.469	1.313	0.906	4.4
2B44SH	A1	4.0	4.4	4.75	SH	0.500" - 1.625"	0.031	1.313	0.406	4.6
2B46SDS	A1	4.2	4.6	4.95	SDS	0.500" - 1.938"	0.031	1.313	0.406	5.0
2B48SDS	A1	4.4	4.8	5.15	SDS	0.500" - 1.938"	0.031	1.313	0.406	5.4
2B50SDS	A1	4.6	5.0	5.35	SDS	0.500" - 1.938"	0.031	1.313	0.406	6.0
2B52SDS	A1	4.8	5.2	5.55	SDS	0.500" - 1.938"	0.031	1.313	0.406	6.3
2B54SDS	A1	5.0	5.4	5.75	SDS	0.500" - 1.938"	0.031	1.313	0.406	6.6
2B56SDS	A2	5.2	5.6	5.95	SDS	0.500" - 1.938"	0.031	1.313	0.406	6.9
2B58SDS	A2	5.4	5.8	6.15	SDS	0.500" - 1.938"	0.031	1.313	0.406	7.2
2B60SDS	A2	5.6	6.0	6.35	SDS	0.500" - 1.938"	0.031	1.313	0.406	7.5
2B62SDS	A2	5.8	6.2	6.55	SDS	0.500" - 1.938"	0.031	1.313	0.406	7.8
2B64SDS	A2	6.0	6.4	6.75	SDS	0.500" - 1.938"	0.031	1.313	0.406	8.2
2B66SDS	A2	6.2	6.6	6.95	SDS	0.500" - 1.938"	0.031	1.313	0.406	8.6
2B68SDS	A3	6.4	6.8	7.15	SDS	0.500" - 1.938"	0.031	1.313	0.406	9.0
2B70SK	D1	6.6	7.0	7.35	SK	0.500" - 2.500"	0.344	1.938	0.156	9.3
2B74SK	D3	7.0	7.4	7.75	SK	0.500" - 2.500"	0.344	1.938	0.156	10.6
2B80SK	D3	7.6	8.0	8.35	SK	0.500" - 2.500"	0.344	1.938	0.156	11.0
2B86SK	D3	8.2	8.6	8.95	SK	0.500" - 2.500"	0.344	1.938	0.156	11.6
2B94SK	D3	9.0	9.4	9.75	SK	0.500" - 2.625"	0.344	1.938	0.156	13.0
2B110SK	D3	10.6	11.0	11.35	SK	0.500" - 2.625"	0.344	1.938	0.156	14.0
2B124SK	D3	12.0	12.4	12.75	SK	0.500" - 2.625"	0.344	1.938	0.156	18.0
2B136SK	D3	13.2	13.6	13.95	SK	0.500" - 2.625"	0.344	1.938	0.156	20.0
2B154SK	D3	15.0	15.4	15.75	SK	0.500" - 2.625"	0.344	1.938	0.156	23.0
2B160SK	D3	15.6	16.0	16.35	SK	0.500" - 2.625"	0.344	1.938	0.156	24.0
2B184SK	D3	18.0	18.4	18.75	SK	0.500" - 2.625"	0.344	1.938	0.156	29.0
2B200SF	D3	19.6	20.0	20.35	SF	0.500" - 2.938"	0.469	2.063	0.156	33.0
2B250SF	D3	24.6	25.0	25.35	SF	0.500" - 2.938"	0.469	2.063	0.156	41.0
2B300SF	D3	29.6	30.0	30.35	SF	0.500" - 2.938"	0.469	2.063	0.156	51.0
2B380SF	D3	37.6	38.0	38.35	SF	0.500" - 2.938"	0.469	2.063	0.156	64.0

TYPE A



TYPE D



TYPE E

