

MXL TIMING PULLEYS

METRIC TIMING PULLEY

2.03mm Trapezoidal Pitch

For 6mm Wide Belts

Hub



Aluminum

Clear Anodized

Metric Finished Bore



Part Number	No. of Teeth	Type	Pitch Dia. (mm)	Out. Dia. (mm)	Flange Dia. (mm)	Bore (mm)	Face Width (mm)	Overall Length (mm)	Hub Dia. (mm)	Set Screw
30MP025M6FA6	30	6F	19.4	18.9	24.0	6.0	9.9	17.5	13.9	2 x M3 @ 90°
30MP025M6FA8	30	6F	19.4	18.9	24.0	8.0	9.9	17.5	13.9	2 x M3 @ 90°
32MP025M6FA6	32	6F	20.7	20.2	25.4	6.0	9.9	17.5	15.2	2 x M3 @ 90°
36MP025M6FA6	36	6F	23.3	22.8	28.1	6.0	9.9	17.5	17.2	2 x M3 @ 90°
40MP025M6FA6	40	6F	25.9	25.4	30.7	6.0	10.3	18.3	19.2	2 x M3 @ 90°
42MP025M6FA6	42	6F	27.2	26.7	32.0	6.0	10.3	18.3	20.5	2 x M3 @ 90°
44MP025M6FA6	44	6F	28.5	28.0	33.4	6.0	10.3	18.3	21.8	2 x M3 @ 90°
48MP025M6FA6	48	6F	31.0	30.5	36.1	6.0	10.3	18.3	23.8	2 x M3 @ 90°
60MP025M6FA6	60	6F	38.8	38.3	43.9	6.0	10.3	18.3	31.0	2 x M3 @ 90°
60MP025M6A6	60	6	38.8	38.3	-	6.0	-	19.1	29.2	2 x M3 @ 90°
72MP025M6A6	72	6	46.6	46.1	-	6.0	-	19.1	30.4	2 x M3 @ 90°
80MP025M6A8	80	6	51.7	51.2	-	8.0	-	19.1	38.1	2 x M4 @ 90°
90MP025M6A8	90	6	58.2	57.7	-	8.0	-	19.1	38.1	2 x M4 @ 90°
100MP025M6A8	100	6	64.7	64.2	-	8.0	-	19.1	38.1	2 x M4 @ 90°
120MP025M6A10	120	6	77.6	77.1	-	10.0	-	19.1	38.1	2 x M5 @ 90°



Save time and money on labels by taking advantage of our custom eco-friendly marking options. Custom marking options are available with our ElectroX Laser Marking Machine, our Epilog Laser Marking Machine, and our Telesis Pin Stamp Marking Machine.