

AT10 TIMING PULLEYS

METRIC TIMING PULLEY

10 mm Pitch

For 16 mm Wide Belts




Hub

Zinc Plated Steel Flanges

Aluminum



Part Number	No. of Teeth	Type	Pitch Dia. (mm)	Out. Dia. (mm)	Flange Dia. (mm)	Bore (mm)	Face Width (mm)	Overall Length (mm)	Hub Dia. (mm)
31AT10/18-2	18	6F	57.3	55.5	60.0	10.0	22.0	31.0	40.0
31AT10/20-2	20	6F	63.7	61.8	66.0	12.0	22.0	31.0	46.0
31AT10/22-2	22	6F	70.0	68.2	66.0	12.0	22.0	31.0	50.0
31AT10/24-2	24	6F	76.4	74.6	83.0	12.0	22.0	31.0	58.0
31AT10/25-2	25	6F	79.6	77.8	83.0	12.0	22.0	31.0	60.0
31AT10/27-2	27	6F	86.0	84.1	91.0	12.0	22.0	31.0	60.0
31AT10/30-2	30	6F	95.5	93.7	97.0	12.0	22.0	31.0	60.0
31AT10/32-2	32	6F	101.9	100.0	106.0	12.0	22.0	31.0	65.0
31AT10/36-2	36	6F	114.6	112.8	119.0	16.0	22.0	31.0	70.0
31AT10/40-2	40	6F	127.3	125.5	131.0	16.0	22.0	31.0	80.0
31AT10/44-2	44	6F	140.1	138.2		16.0	22.0	31.0	90.0
31AT10/48-0	48	6	152.8	151.0	-	16.0	22.0	31.0	95.0
31AT10/60-0	60	6	191.0	189.1	-	16.0	22.0	31.0	110.0



For matching AT10 pitch belts,
see page 213.



For AT10 pitch pulley stock,
see page 369.

The AT10 pitch is a metric pitch tooth profile and is trapezoidal in shape. AT10 pitch pulley part numbers can tell you a great deal about the pulley including the number of teeth, pitch, overall length, and number of flanges.

For more information on part numbers and their meaning,
see page 441.