

POWERHOUSE™

TIMING PULLEYS

(Compatible with PowerGrip® GT2® and PowerGrip® GT3® pitches)

5 mm Pitch
For 15 mm Wide Belts
Flanges
Steel/Iron
Black Oxide Plating



| Part Number | No. of Teeth | Type | Pitch Dia. (in) | Out. Dia. (in) | Flange Dia. (in) | Bore / Bushing | Face Width (in) | Overall Length (in) | Hub Dia. (in) |
|---------------|--------------|------|-----------------|----------------|------------------|----------------|-----------------|---------------------|---------------|
| 18-5P15-6FS3 | 18 | 6F | 1.128 | 1.083 | 1.375 | 0.250" | 0.890 | 1.250 | 0.680 |
| 19-5P15-6FS3 | 19 | 6F | 1.191 | 1.146 | 1.438 | 0.250" | 0.890 | 1.250 | 0.880 |
| 20-5P15-6FS3 | 20 | 6F | 1.253 | 1.208 | 1.531 | 0.250" | 0.890 | 1.250 | 0.900 |
| 21-5P15-6FS3 | 21 | 6F | 1.316 | 1.271 | 1.531 | 0.250" | 0.890 | 1.250 | 0.900 |
| 22-5P15-6FS3 | 22 | 6F | 1.379 | 1.334 | 1.656 | 0.250" | 0.890 | 1.280 | 0.940 |
| 23-5P15-6FS5 | 23 | 6F | 1.441 | 1.396 | 1.656 | 0.375" | 0.890 | 1.280 | 1.150 |
| 24-5P15-6FS5 | 24 | 6F | 1.504 | 1.459 | 1.781 | 0.375" | 0.890 | 1.280 | 1.180 |
| 25-5P15-6FS5 | 25 | 6F | 1.566 | 1.521 | 1.781 | 0.375" | 0.890 | 1.280 | 1.180 |
| 26-5P15-6FS5 | 26 | 6F | 1.629 | 1.584 | 1.906 | 0.375" | 0.890 | 1.280 | 1.210 |
| 28-5P15-6FS6 | 28 | 6F | 1.754 | 1.709 | 2.031 | 0.500" | 0.890 | 1.340 | 1.370 |
| 30-5P15-6FS6 | 30 | 6F | 1.880 | 1.835 | 2.125 | 0.500" | 0.890 | 1.340 | 1.440 |
| 32-5P15-6FS6 | 32 | 6F | 2.005 | 1.960 | 2.125 | 0.500" | 0.890 | 1.340 | 1.440 |
| 34-5P15-6FS6 | 34 | 6F | 2.130 | 2.085 | 2.375 | 0.500" | 0.890 | 1.340 | 1.690 |
| 36-5P15-6FS6 | 36 | 6F | 2.256 | 2.211 | 2.375 | 0.500" | 0.890 | 1.340 | 1.690 |
| 38-5P15-6FS6 | 38 | 6F | 2.381 | 2.336 | 2.625 | 0.500" | 0.890 | 1.340 | 1.960 |
| 40-5P15-6FS6 | 40 | 6F | 2.506 | 2.461 | 2.750 | 0.500" | 0.890 | 1.380 | 2.090 |
| 45-5P15-6FS6 | 45 | 6F | 2.820 | 2.775 | 3.094 | 0.500" | 0.890 | 1.380 | 2.340 |
| 50-5P15-6FS6 | 50 | 6F | 3.133 | 3.088 | 3.330 | 0.500" | 0.890 | 1.380 | 2.500 |
| 36-5P15-1108 | 36 | A1F | 2.256 | 2.211 | 2.375 | 1108 | 0.880 | 0.880 | - |
| 38-5P15-1108 | 38 | A1F | 2.381 | 2.336 | 2.625 | 1108 | 0.880 | 0.880 | - |
| 40-5P15-1108 | 40 | A1F | 2.506 | 2.461 | 2.750 | 1108 | 0.880 | 0.880 | - |
| 44-5P15-1108 | 44 | A1F | 2.757 | 2.712 | 3.094 | 1108 | 0.880 | 0.880 | - |
| 48-5P15-1210 | 48 | A1F | 3.008 | 2.963 | 3.330 | 1210 | 0.880 | 1.000 | - |
| 52-5P15-1210 | 52 | B1F | 3.258 | 3.213 | 3.566 | 1210 | 0.880 | 1.000 | - |
| 56-5P15-1610 | 56 | B1F | 3.509 | 3.464 | 3.800 | 1610 | 0.880 | 1.000 | - |
| 60-5P15-1610 | 60 | B1F | 3.760 | 3.715 | 4.044 | 1610 | 0.880 | 1.000 | - |
| 64-5P15-1610 | 64 | B1F | 4.010 | 3.965 | 4.170 | 1610 | 0.880 | 1.000 | - |
| 68-5P15-1610 | 68 | B1F | 4.261 | 4.216 | 4.520 | 1610 | 0.880 | 1.000 | - |
| 72-5P15-1610 | 72 | B1F | 4.511 | 4.466 | 4.670 | 1610 | 0.880 | 1.000 | - |
| 80-5P15-1610 | 80 | B1 | 5.013 | 4.968 | - | 1610 | 0.880 | 1.000 | - |
| 90-5P15-1610 | 90 | B1 | 5.639 | 5.594 | - | 1610 | 0.880 | 1.000 | - |
| 112-5P15-2012 | 112 | B1 | 7.018 | 6.973 | - | 2012 | 0.880 | 1.250 | - |

