

T10 TIMING PULLEYS

METRIC TIMING PULLEY

10 mm Pitch

For 16 mm Wide Belts




Hub

Zinc Plated Steel Flanges


Aluminum



Part Number	No. of Teeth	Type	Pitch Dia. (mm)	Out. Dia. (mm)	Flange Dia. (mm)	Bore (mm)	Face Width (mm)	Overall Length (mm)	Hub Dia. (mm)
31T10/14-2	14	6F	44.6	42.7	48.0	8.0	21.0	31.0	32.0
31T10/15-2	15	6F	47.8	45.9	51.0	8.0	21.0	31.0	32.0
31T10/16-2	16	6F	50.9	49.1	54.0	8.0	21.0	31.0	35.0
31T10/18-2	18	6F	57.3	55.5	60.0	8.0	21.0	31.0	40.0
31T10/19-2	19	6F	60.5	58.7	66.0	8.0	21.0	31.0	44.0
31T10/20-2	20	6F	63.7	61.8	66.0	8.0	21.0	31.0	46.0
31T10/24-2	24	6F	76.4	74.6	83.0	8.0	21.0	31.0	58.0
31T10/25-2	25	6F	79.6	77.8	83.0	8.0	21.0	31.0	60.0
31T10/27-2	27	6F	86.0	84.1	91.0	8.0	21.0	31.0	60.0
31T10/30-2	30	6F	95.5	93.7	97.0	8.0	21.0	31.0	60.0
31T10/32-2	32	6F	101.9	100.0	106.0	10.0	21.0	31.0	65.0
31T10/36-2	36	6F	114.6	112.8	119.0	10.0	21.0	31.0	70.0
31T10/40-2	40	6F	127.3	125.5	131.0	10.0	21.0	31.0	80.0
31T10/48-0	48	6	152.8	151.0	-	16.0	21.0	31.0	95.0
31T10/60-0	60	6	191.0	189.2	-	16.0	21.0	31.0	110.0



For T10 pitch pulley stock, see page 336.



For matching T10 pitch belts, see page 208.

The T10 pitch is a metric pitch tooth profile and is trapezoidal in shape. T10 pitch pulley part numbers can tell you a great deal about the pulley including the number of teeth, pitch, overall length, and number of flanges.

For more information on part numbers and their meaning, see page 441.