

XL TIMING PULLEYS

0.200" Trapezoidal Pitch


For 3/8" Wide Belts

Hub and Flanges



Aluminum

Clear Anodized


Finished Bore



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bore (in)	Face Width (in)	Overall Length (in)	Hub Dia. (in)	Set Screw
26XL037-6FA3	26	6F	1.665	1.635	1.875	0.250	0.563	0.906	1.188	2 x 8-32 @ 90°
26XL037-6FA4	26	6F	1.665	1.635	1.875	0.313	0.563	0.906	1.188	2 x 8-32 @ 90°
26XL037-6FA5	26	6F	1.665	1.635	1.875	0.375	0.563	0.906	1.188	2 x 10-32 @ 90°
26XL037-6FA6	26	6F	1.665	1.635	1.875	0.500	0.563	0.906	1.188	2 x 10-32 @ 90°
28XL037-6FA3	28	6F	1.783	1.763	2.000	0.250	0.563	0.906	1.188	2 x 8-32 @ 90°
28XL037-6FA4	28	6F	1.783	1.763	2.000	0.313	0.563	0.906	1.188	2 x 8-32 @ 90°
28XL037-6FA5	28	6F	1.783	1.763	2.000	0.375	0.563	0.906	1.188	2 x 10-32 @ 90°
28XL037-6FA6	28	6F	1.783	1.763	2.000	0.500	0.563	0.906	1.188	2 x 10-32 @ 90°
28XL037-6FA7	28	6F	1.783	1.763	2.000	0.625	0.563	0.906	1.188	2 x 10-32 @ 90°
30XL037-6FA3	30	6F	1.910	1.890	2.125	0.250	0.563	0.906	1.312	2 x 8-32 @ 90°
30XL037-6FA4	30	6F	1.910	1.890	2.125	0.313	0.563	0.906	1.312	2 x 8-32 @ 90°
30XL037-6FA5	30	6F	1.910	1.890	2.125	0.375	0.563	0.906	1.312	2 x 10-32 @ 90°
30XL037-6FA6	30	6F	1.910	1.890	2.125	0.500	0.563	0.906	1.312	2 x 10-32 @ 90°
30XL037-6FA7	30	6F	1.910	1.890	2.125	0.625	0.563	0.906	1.312	2 x 10-32 @ 90°
32XL037-6FA3	32	6F	2.037	2.017	2.250	0.250	0.563	0.906	1.437	2 x 10-32 @ 90°
32XL037-6FA4	32	6F	2.037	2.017	2.250	0.313	0.563	0.906	1.437	2 x 10-32 @ 90°
32XL037-6FA5	32	6F	2.037	2.017	2.250	0.375	0.563	0.906	1.437	2 x 10-32 @ 90°
32XL037-6FA6	32	6F	2.037	2.017	2.250	0.500	0.563	0.906	1.437	2 x 10-32 @ 90°
32XL037-6FA7	32	6F	2.037	2.017	2.250	0.625	0.563	0.906	1.437	2 x 10-32 @ 90°



For matching XL pitch belts, see page 187.



At B&B Manufacturing, we have an extensive online catalog of off-the-shelf parts that meet a wide variety of needs in the power transmission and precision mechanical component marketplaces.

But we know that sometimes it takes something special to do the job right. That's why we can modify any of our stock components to meet your unique performance and material specifications. We also offer fast, precision-engineered and quality manufactured components that can be built from the ground up in the B&B Manufacturing Custom Shop.