

XL TIMING PULLEYS

0.200" Trapezoidal Pitch


For 3/8" Wide Belts

Hubless With Flanges

Aluminum


Clear Anodized

Finished Bore



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bore (in)	Overall Length (in)	Set Screw
20XL037-3FA3	20	3F	1.273	1.253	1.500	0.250	0.563	2 x 8-32 @ 90°
20XL037-3FA4	20	3F	1.273	1.253	1.500	0.313	0.563	2 x 8-32 @ 90°
20XL037-3FA5	20	3F	1.273	1.253	1.500	0.375	0.563	2 x 8-32 @ 90°
20XL037-3FA6	20	3F	1.273	1.253	1.500	0.500	0.563	2 x 8-32 @ 90°
20XL037-3FA7	20	3F	1.273	1.253	1.500	0.625	0.563	2 x 8-32 @ 90°
21XL037-3FA3	21	3F	1.337	1.317	1.563	0.250	0.563	2 x 8-32 @ 90°
21XL037-3FA4	21	3F	1.337	1.317	1.563	0.313	0.563	2 x 8-32 @ 90°
21XL037-3FA5	21	3F	1.337	1.317	1.563	0.375	0.563	2 x 8-32 @ 90°
21XL037-3FA6	21	3F	1.337	1.317	1.563	0.500	0.563	2 x 8-32 @ 90°
22XL037-3FA3	22	3F	1.401	1.381	1.625	0.250	0.563	2 x 8-32 @ 90°
22XL037-3FA4	22	3F	1.401	1.381	1.625	0.313	0.563	2 x 8-32 @ 90°
22XL037-3FA5	22	3F	1.401	1.381	1.625	0.375	0.563	2 x 8-32 @ 90°
22XL037-3FA6	22	3F	1.401	1.381	1.625	0.500	0.563	2 x 8-32 @ 90°
24XL037-3FA3	24	3F	1.528	1.508	1.750	0.250	0.563	2 x 8-32 @ 90°
24XL037-3FA4	24	3F	1.528	1.508	1.750	0.313	0.563	2 x 8-32 @ 90°
24XL037-3FA5	24	3F	1.528	1.508	1.750	0.375	0.563	2 x 8-32 @ 90°
24XL037-3FA6	24	3F	1.528	1.508	1.750	0.500	0.563	2 x 8-32 @ 90°
28XL037-3FA3	28	3F	1.783	1.763	2.000	0.250	0.563	2 x 8-32 @ 90°
28XL037-3FA4	28	3F	1.783	1.763	2.000	0.313	0.563	2 x 8-32 @ 90°
28XL037-3FA5	28	3F	1.783	1.763	2.000	0.375	0.563	2 x 8-32 @ 90°
28XL037-3FA6	28	3F	1.783	1.763	2.000	0.500	0.563	2 x 8-32 @ 90°
30XL037-3FA3	30	3F	1.910	1.890	2.125	0.250	0.563	2 x 8-32 @ 90°
30XL037-3FA4	30	3F	1.910	1.890	2.125	0.313	0.563	2 x 8-32 @ 90°
30XL037-3FA5	30	3F	1.910	1.890	2.125	0.375	0.563	2 x 8-32 @ 90°
30XL037-3FA6	30	3F	1.910	1.890	2.125	0.500	0.563	2 x 8-32 @ 90°
30XL037-3FA7	30	3F	1.910	1.890	2.125	0.625	0.563	2 x 8-32 @ 90°
32XL037-3FA3	32	3F	2.037	2.017	2.250	0.250	0.563	2 x 8-32 @ 90°
32XL037-3FA4	32	3F	2.037	2.017	2.250	0.313	0.563	2 x 8-32 @ 90°
32XL037-3FA5	32	3F	2.037	2.017	2.250	0.375	0.563	2 x 8-32 @ 90°
32XL037-3FA6	32	3F	2.037	2.017	2.250	0.500	0.563	2 x 8-32 @ 90°
32XL037-3FA7	32	3F	2.037	2.017	2.250	0.625	0.563	2 x 8-32 @ 90°

TYPE 3F



Using Lean Manufacturing and CONWIP production control systems, B&B Manufacturing strives to eliminate waste in costs, tooling and processes. B&B Manufacturing constantly monitors our processes in an effort to continuously improve our lead times, quality control, and costs. By combining Lean Manufacturing with a CONWIP (A hybrid push-pull kanban system) production control system, B&B Manufacturing is constantly improving upon our Just in Time production strategy to deliver precision mechanical components and Power Transmission parts to our clients when they need them.