


# T10 TIMING PULLEY BAR STOCK

T10 mm Pitch  
Aluminum

METRIC TIMING PULLEY STOCK



Timing Pulley Stock

Part Number	No. of Teeth	Metric		Inch		Shank Diameter	Shank Length	Minimum Usable Length	Overall Length
		Pitch Diameter	Outside Diameter	Pitch Diameter	Outside Diameter				
10T10-PS140A	10	32.0 mm	30.0 mm	1.259"	1.180"	0.500"	1.600"	5.500"	7.100"
11T10-PS140A	11	35.2 mm	33.2 mm	1.384"	1.306"	0.500"	1.600"	5.500"	7.100"
12T10-PS140A	12	38.4 mm	36.3 mm	1.510"	1.431"	0.500"	1.600"	5.500"	7.100"
13T10-PS140A	13	41.5 mm	39.5 mm	1.634"	1.555"	0.500"	1.600"	5.500"	7.100"
14T10-PS160A	14	44.7 mm	42.7 mm	1.760"	1.681"	0.500"	0.800"	6.300"	7.100"
15T10-PS160A	15	47.9 mm	45.9 mm	1.886"	1.807"	0.500"	0.800"	6.300"	7.100"
16T10-PS160A	16	51.1 mm	49.0 mm	2.010"	1.931"	0.500"	0.800"	6.300"	7.100"
17T10-PS160A	17	54.3 mm	52.2 mm	2.136"	2.057"	0.500"	0.800"	6.300"	7.100"
18T10-PS160A	18	57.5 mm	55.4 mm	2.262"	2.183"	0.750"	1.000"	6.300"	7.300"
19T10-PS160A	19	60.6 mm	58.6 mm	2.386"	2.307"	0.750"	1.000"	6.300"	7.300"
20T10-PS160A	20	63.8 mm	61.8 mm	2.512"	2.433"	0.750"	1.000"	6.300"	7.300"
21T10-PS160A	21	67.0 mm	65.0 mm	2.638"	2.559"	0.750"	1.000"	6.300"	7.300"
22T10-PS160A	22	70.2 mm	68.1 mm	2.762"	2.683"	0.750"	1.000"	6.300"	7.300"
23T10-PS160A	23	73.4 mm	71.3 mm	2.888"	2.809"	0.750"	1.000"	6.300"	7.300"
24T10-PS160A	24	76.6 mm	74.3 mm	3.014"	2.927"	0.750"	1.000"	6.300"	7.300"
26T10-PS160A	26	82.9 mm	80.9 mm	3.264"	3.185"	0.750"	1.000"	6.300"	7.300"
28T10-PS160A	28	89.3 mm	87.2 mm	3.514"	3.435"	0.750"	1.000"	6.300"	7.300"
30T10-PS160A	30	95.7 mm	93.6 mm	3.766"	3.687"	0.750"	1.000"	6.300"	7.300"
32T10-PS160A	32	102.0 mm	100.0 mm	4.016"	3.937"	0.750"	1.000"	6.300"	7.300"
34T10-PS160A	34	108.4 mm	106.4 mm	4.268"	4.189"	1.000"	1.000"	6.300"	7.300"
36T10-PS160A	36	114.8 mm	112.8 mm	4.518"	4.439"	1.000"	1.000"	6.300"	7.300"
38T10-PS160A	38	121.1 mm	119.1 mm	4.768"	4.689"	1.000"	1.000"	6.300"	7.300"
40T10-PS160A	40	127.5 mm	125.5 mm	5.018"	4.939"	1.000"	1.000"	6.300"	7.300"
45T10-PS160A	45	143.4 mm	141.4 mm	5.646"	5.567"	1.000"	1.000"	6.300"	7.300"
48T10-PS160A	48	153.0 mm	151.0 mm	6.022"	5.943"	1.000"	1.000"	6.300"	7.300"
60T10-PS160A	60	191.1 mm	189.1 mm	7.524"	7.445"	1.000"	1.000"	6.300"	7.300"
72T10-PS160A	72	229.3 mm	227.3 mm	9.027"	8.948"	1.000"	1.000"	6.300"	7.300"