

L TIMING PULLEYS

0.375" Trapezoidal Pitch

For 1" Wide Belts

Steel/Iron

Split Taper Style



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bushing	Face Width (in)	Overall Length (in)
18LG100	18	4	2.149	2.119	2.438	G	1.250	1.875
19LG100	19	4	2.268	2.238	2.625	G	1.250	1.875
20LG100	20	4	2.387	2.357	2.625	G	1.250	1.875
21LG100	21	4	2.507	2.477	2.875	G	1.250	1.875
22LG100	22	4	2.626	2.596	2.875	G	1.250	1.875
24LH100	24	4	2.865	2.835	3.125	H	1.250	1.875
26LH100	26	4	3.104	3.074	3.375	H	1.250	1.875
28LH100	28	4	3.342	3.312	3.625	H	1.250	1.875
30LH100	30	16	3.581	3.551	3.813	H	1.250	1.438
32LH100	32	16	3.820	3.790	4.063	H	1.250	1.438
36LH100	36	16	4.297	4.267	4.688	H	1.250	1.438
36LP100	36	6	4.297	4.267	4.688	P1	1.250	2.188
40LH100	40	16	4.775	4.745	5.000	H	1.250	1.438
40LP100	40	6	4.775	4.745	5.000	P1	1.250	2.188
44LH100	44	16	5.285	5.222	5.500	H	1.250	1.438
44LP100	44	6	5.252	5.222	5.500	P1	1.250	2.188
48LH100	48	16	5.730	5.700	6.000	H	1.250	1.438
48LP100	48	6	5.730	5.700	6.000	P1	1.250	2.188
60LH100	60	18	7.162	7.132	-	H	1.250	1.500
60LP100	60	13	7.162	7.132	-	P1	1.250	2.188
72LH100	72	18	8.594	8.564	-	H	1.250	1.500
72LP100	72	13	8.594	8.564	-	P1	1.250	2.188
84LH100	84	18	10.027	9.997	-	H	1.250	1.500
84LP100	84	13	10.027	9.997	-	P1	1.250	2.188
96LH100	96	18	11.459	11.429	-	H	1.250	1.500
96LP100	96	13	11.459	11.429	-	P1	1.250	2.188
120LH100	120	18	14.324	14.294	-	H	1.250	1.500
120LP100	120	13	14.324	14.294	-	P1	1.250	2.188

