

T10 TIMING PULLEYS

10 mm Pitch


For 25 mm Wide Belts

Hub




Zinc Plated Steel Flanges

Aluminum


METRIC TIMING PULLEY



Part Number	No. of Teeth	Type	Pitch Dia (mm)	Out. Dia. (mm)	Flange Dia (mm)	Bore (mm)	Face Width (mm)	Overall Length (mm)	Hub Dia. (mm)
40T10/14-2	14	6F	44.6	42.7	48.0	8.0	30.0	40.0	32.0
40T10/15-2	15	6F	47.8	45.9	51.0	8.0	30.0	40.0	32.0
40T10/16-2	16	6F	50.9	49.1	54.0	8.0	30.0	40.0	35.0
40T10/18-2	18	6F	57.3	55.5	60.0	8.0	30.0	40.0	40.0
40T10/19-2	19	6F	60.5	58.7	66.0	8.0	30.0	40.0	44.0
40T10/20-2	20	6F	63.7	61.8	66.0	8.0	30.0	40.0	46.0
40T10/24-2	24	6F	76.4	74.6	83.0	8.0	30.0	40.0	58.0
40T10/25-2	25	6F	79.6	77.8	83.0	8.0	30.0	40.0	60.0
40T10/27-2	27	6F	86.0	84.1	91.0	8.0	30.0	40.0	60.0
40T10/30-2	30	6F	95.5	93.7	97.0	8.0	30.0	40.0	60.0
40T10/32-2	32	6F	101.9	100.0	106.0	10.0	30.0	40.0	65.0
40T10/36-2	36	6F	114.6	112.8	119.0	10.0	30.0	40.0	70.0
40T10/40-2	40	6F	127.3	125.5	131.0	10.0	30.0	40.0	80.0
40T10/48-0	48	6	152.8	151.0	-	16.0	30.0	40.0	95.0
40T10/60-0	60	6	191.0	189.2	-	16.0	30.0	40.0	110.0



B&B Manufacturing can provide custom bore finishing to your specifications. We can provide custom bore finishing for a single part or thousands of parts. Our bore finisher can handle nearly any materials in nearly any shape and provide precision sizing and geometric accuracy with nearly any surface finish.



For matching T10 pitch belts, see page 208.