

POWERHOUSE™ TIMING PULLEYS

(Compatible with PowerGrip® GT2® and PowerGrip® GT3® pitches)

5 mm Pitch
For 25 mm Wide Belts
Flanges
Steel/Iron
Black Oxide Plating



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bore / Bushing	Face Width (in)	Overall Length (in)	Hub Dia. (in)
18-5P25-6FS3	18	6F	1.128	1.083	1.375	0.250"	1.280	1.650	0.680
19-5P25-6FS3	19	6F	1.191	1.146	1.438	0.250"	1.280	1.650	0.880
20-5P25-6FS3	20	6F	1.253	1.208	1.531	0.250"	1.280	1.650	0.900
21-5P25-6FS3	21	6F	1.316	1.271	1.531	0.250"	1.280	1.650	0.900
22-5P25-6FS3	22	6F	1.379	1.334	1.656	0.250"	1.280	1.680	0.940
23-5P25-6FS5	23	6F	1.441	1.396	1.656	0.375"	1.280	1.680	1.150
24-5P25-6FS5	24	6F	1.504	1.459	1.781	0.375"	1.280	1.680	1.180
25-5P25-6FS5	25	6F	1.566	1.521	1.781	0.375"	1.280	1.680	1.180
26-5P25-6FS5	26	6F	1.629	1.584	1.906	0.375"	1.280	1.680	1.210
28-5P25-6FS6	28	6F	1.754	1.709	2.031	0.375"	1.280	1.730	1.370
30-5P25-6FS6	30	6F	1.880	1.835	2.125	0.500"	1.280	1.730	1.440
32-5P25-6FS6	32	6F	2.005	1.960	2.125	0.500"	1.280	1.730	1.440
34-5P25-6FS6	34	6F	2.130	2.085	2.375	0.500"	1.280	1.730	1.690
36-5P25-6FS6	36	6F	2.256	2.211	2.375	0.500"	1.280	1.730	1.690
38-5P25-6FS6	38	6F	2.381	2.336	2.625	0.500"	1.280	1.730	1.960
40-5P25-6FS6	40	6F	2.506	2.461	2.750	0.500"	1.280	1.780	2.090
45-5P25-6FS6	45	6F	2.820	2.775	3.094	0.500"	1.280	1.780	2.340
50-5P25-6FS6	50	6F	3.133	3.088	3.330	0.500"	1.280	1.780	2.500
36-5P25-1108	36	A1F	2.256	2.211	2.375	1108	1.290	1.290	-
38-5P25-1108	38	A1F	2.381	2.336	2.625	1108	1.290	1.290	-
40-5P25-1108	40	A1F	2.506	2.461	2.750	1108	1.290	1.290	-
44-5P25-1108	44	A1F	2.757	2.712	3.094	1108	1.290	1.290	-
48-5P25-1210	48	A1F	3.008	2.963	3.330	1210	1.280	1.280	-
52-5P25-1210	52	A1F	3.258	3.213	3.566	1210	1.280	1.280	-
56-5P25-1610	56	A1F	3.509	3.464	3.800	1610	1.280	1.280	-
60-5P25-1610	60	A1F	3.760	3.715	4.044	1610	1.280	1.280	-
64-5P25-1610	64	A1F	4.010	3.965	4.170	1610	1.280	1.280	-
68-5P25-2012	68	A1F	4.261	4.216	4.520	2012	1.280	1.280	-
72-5P25-2012	72	A1F	4.511	4.466	4.670	2012	1.280	1.280	-
80-5P25-2012	80	A1	5.013	4.968	-	2012	1.280	1.280	-
90-5P25-2012	90	A1	5.639	5.594	-	2012	1.280	1.280	-
112-5P25-2012	112	A1	7.018	6.973	-	2012	1.280	1.280	-

