



# POWERHOUSE MX™ TIMING PULLEYS

(Compatible with Poly Chain® GT® Carbon belts)


**8 mm Pitch**  
**For 12 mm Wide Belts**  
**Flanges**  
**Steel/Iron**  
**Black Oxide Plating**  
**Taper-Lock® Style**



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bore/Bushing	Face Width (in)	Overall Length (in)
22-8MX12-1008	22	A1F	2.206	2.143	2.559	1008	0.875	0.875
22-8MX12-6FS6	22	6F	2.206	2.143	2.559	0.500	0.850	1.313
25-8MX12-1108	25	A1F	2.506	2.443	2.953	1108	0.875	0.875
25-8MX12-6FS6	25	6F	2.506	2.443	2.953	0.500	0.850	1.313
26-8MX12-1108	26	A1F	2.607	2.544	2.953	1108	0.875	0.875
27-8MX12-1108	27	A1F	2.707	2.644	3.150	1108	0.875	0.875
28-8MX12-1108	28	A1F	2.807	2.744	3.150	1108	0.875	0.875
28-8MX12-6FS6	28	6F	2.807	2.744	3.150	0.500	0.850	1.313
29-8MX12-1108	29	A1F	2.907	2.844	3.346	1108	0.875	0.875
30-8MX12-1108	30	A1F	3.008	2.945	3.346	1108	0.875	0.875
30-8MX12-6FS6	30	6F	3.008	2.945	3.346	0.500	0.850	1.422
31-8MX12-1210	31	A1F	3.108	3.045	3.543	1210	1.000	1.000
32-8MX12-1210	32	A1F	3.208	3.145	3.543	1210	1.000	1.000
32-8MX12-6FS6	32	6F	3.208	3.145	3.543	0.500	0.850	1.422
33-8MX12-1610	33	A1F	3.308	3.245	3.819	1610	1.000	1.000
34-8MX12-1610	34	A1F	3.409	3.346	3.819	1610	1.000	1.000
35-8MX12-1610	25	A1F	3.509	3.446	3.938	1610	1.000	1.000
36-8MX12-1610	36	A1F	3.609	3.546	3.938	1610	1.000	1.000



Whether you need a custom part made from heat treated steel or you need your custom part with its teeth hardened, the B&B Manufacturing Custom Shop can meet your custom requirements.



For matching 8MX pitch belts, see page 246.