

# H TIMING PULLEYS

0.500" Trapezoidal Pitch


For 3" Wide Belts

Steel/Iron

Split Taper Bore




Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bushing	Face Width (in)	Overall Length (in)
32HQ300	32	11	5.093	5.039	5.313	Q1	3.313	3.594
38HQ300	38	11	5.730	5.876	6.000	Q1	3.313	3.594
40HQ300	40	11	6.386	6.312	6.563	Q1	3.313	3.594
44HQ300	44	11	7.003	6.949	7.250	Q1	3.313	3.594
48HQ300	48	11	7.639	7.585	7.875	Q1	3.313	3.594
60HQ300	60	15	9.549	9.495	-	Q1	3.313	3.563
72HQ300	72	15	11.459	11.405	-	Q1	3.313	3.563
84HQ300	84	15	13.369	13.315	-	Q1	3.313	3.563
96HR300	96	14	15.279	15.225	-	R1	3.313	3.813
120HR300	120	14	19.099	19.045	-	R1	3.313	3.813
156HR300	156	14	24.828	24.774	-	R1	3.500	3.906




At B&B Manufacturing, we have an extensive online catalog of off-the-shelf parts that meet a wide variety of needs in the power transmission and precision mechanical marketplaces.

But we know that sometimes it takes something special to do the job right. That's why we can modify any of our stock components to meet your unique performance and material specifications. We also offer fast, precision-engineered and quality manufactured components that can be built from the ground up in our custom shop.

TYPE 11



TYPE 14



TYPE 15

