

L TIMING PULLEYS

0.375" Trapezoidal Pitch




For 0.500" Wide Belts

Steel/Iron

Split Taper Style



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bushing	Face Width (in)	Overall Length (in)
18LG050	18	4	2.149	2.119	2.438	G	0.750	1.375
19LG050	19	4	2.268	2.238	2.625	G	0.750	1.375
20LG050	20	4	2.387	2.357	2.625	G	0.750	1.375
21LG050	21	4	2.507	2.477	2.875	G	0.750	1.375
22LG050	22	4	2.626	2.596	2.875	G	0.750	1.375
24LH050	24	5	2.865	2.835	3.125	H	0.750	1.438
26LH050	26	5	3.104	3.074	3.375	H	0.750	1.438
28LH050	28	5	3.342	3.312	3.625	H	0.750	1.438
30LH050	30	5	3.581	3.551	3.813	H	0.750	1.438
32LH050	32	5	3.820	3.790	4.063	H	0.750	1.438
36LH050	36	5	4.297	4.267	4.688	H	0.750	1.438
36LP050	36	7	4.297	4.267	4.688	P1	0.750	2.188
40LH050	40	5	4.775	4.745	5.000	H	0.750	1.438
40LP050	40	7	4.775	4.745	5.000	P1	0.750	2.188
44LH050	44	5	5.285	5.222	5.500	H	0.750	1.438
44LP050	44	7	5.252	5.222	5.500	P1	0.750	2.188
48LH050	48	5	5.730	5.700	6.000	H	0.750	1.438
48LP050	48	7	5.730	5.700	6.000	P1	0.750	2.188
60LH050	60	17	7.162	7.132	-	H	0.750	1.500
60LP050	60	13	7.162	7.132	-	P1	0.750	2.188
72LH050	72	17	8.594	8.564	-	H	0.750	1.500
72LP050	72	13	8.594	8.564	-	P1	0.750	2.188
84LH050	84	17	10.027	9.997	-	H	0.750	1.500
84LP050	84	13	10.027	9.997	-	P1	0.750	2.188
96LH050	96	17	11.459	11.429	-	H	0.750	1.500
96LP050	96	13	11.459	11.429	-	P1	0.750	2.188
120LH050	120	17	14.324	14.294	-	H	0.750	1.500
120LP050	120	13	14.324	14.294	-	P1	0.750	2.188



For matching Split Taper bushings, see page 374.