

# 3V V-BELT SHEAVES

For 3V V-Belts

3 Grooves

1.500" Face Width


Cast Iron

QD® Style




Part Number	Type	Pitch Dia. "3V" Belts (in)	Out. Dia. (in)	Bushing	Bore Range	E	L	M	Wt. Ea. (Lbs.)
33V250JA	E1	2.45	2.50	JA	0.500" - 1.250"	1.406	1.000	0.906	0.8
33V265JA	D1	2.60	2.65	JA	0.500" - 1.250"	0.375	1.000	0.875	1.0
33V280JA	D1	2.75	2.80	JA	0.500" - 1.250"	0.375	1.000	0.875	1.4
33V300JA	E1	2.95	3.00	JA	0.500" - 1.625"	1.156	1.313	0.969	1.7
33V315SH	E1	3.10	3.15	SH	0.500" - 1.625"	1.156	1.313	0.969	1.8
33V335SH	D1	3.30	3.35	SH	0.500" - 1.625"	0.531	1.313	0.719	1.9
33V365SH	D1	3.60	3.65	SH	0.500" - 1.625"	0.531	1.313	0.719	2.3
33V412SH	A1	4.07	4.12	SH	0.500" - 1.625"	0.031	1.313	0.156	2.6
33V450SDS	A1	4.45	4.50	SDS	0.500" - 2.000"	0.031	1.313	0.156	3.5
33V475SDS	A1	4.70	4.75	SDS	0.500" - 2.000"	0.031	1.313	0.156	4.0
33V500SDS	A1	4.95	5.00	SDS	0.500" - 2.000"	0.031	1.313	0.156	4.5
33V530SDS	A1	5.25	5.30	SDS	0.500" - 2.000"	0.031	1.313	0.156	5.2
33V560SDS	A1	5.55	5.60	SDS	0.500" - 2.000"	0.031	1.313	0.156	6.0
33V600SDS	A2	5.95	6.00	SDS	0.500" - 2.000"	0.031	1.313	0.156	7.0
33V650SDS	A2	6.45	6.50	SDS	0.500" - 2.000"	0.031	1.313	0.156	8.1
33V690SDS	A2	6.85	6.90	SDS	0.500" - 2.000"	0.031	1.313	0.156	8.9
33V800SK	D2	7.95	8.00	SK	0.500" - 2.625"	0.531	1.938	0.094	11.3
33V1060SK	D3	10.55	10.60	SK	0.500" - 2.625"	0.531	1.938	0.094	14.0
33V1400SK	D3	13.95	14.00	SK	0.500" - 2.625"	0.531	1.938	0.094	21.6
33V1900SF	D3	18.95	19.00	SF	0.500" - 2.938"	0.594	2.063	0.031	32.1
33V2500SF	D3	24.95	25.00	SF	0.500" - 2.938"	0.594	2.063	0.031	50.0
33V3350SF	D3	33.45	33.50	SF	0.500" - 2.938"	0.594	2.063	0.031	78.0

**TYPE A**



**TYPE D**



**TYPE E**

