

IDLER SPROCKETS

Needle Bearing

Steel/Iron

Clear Zinc Plating



Part Number	No. of Teeth	Diametral Pitch	Pitch Dia. (in)	Out. Dia. (in)	Bore (in)	Face Width (in)	Overall Length (in)
25B19-IDLER	19	No. 25 (0.250")	1.519"	1.650"	0.500"	0.750"	0.500"
35B19-IDLER	19	No. 35 (0.375")	2.278"	2.470"	1.000"	1.000"	1.000"
41B19-IDLER	19	No. 41 (0.500")	3.038"	3.280"	1.000"	1.000"	1.000"
60B17-IDLER	17	No. 60 (0.750")	4.082"	4.460"	1.000"	1.000"	1.000"
80B13-IDLER	13	No. 80 (1.000")	4.138"	4.660"	1.000"	1.250"	1.250"
100B11-IDLER	11	No. 100 (1.250")	4.377"	5.010"	1.500"	1.875"	1.875"
120B11-IDLER	11	No. 120 (1.500")	5.252"	6.010"	1.500"	2.000"	2.000"
140B11-IDLER	11	No. 140 (1.750")	6.127"	7.010"	1.500"	2.250"	2.250"
35DB19-IDLER	19	No. 35 (0.375")	2.278"	2.470"	1.000"	1.000"	1.000"
40DB19-IDLER	19	No. 40 (0.500")	3.038"	3.280"	1.000"	1.250"	1.250"
50DB17-IDLER	17	No. 50 (0.625")	3.401"	3.720"	1.000"	1.375"	1.375"
60DB17-IDLER	17	No. 60 (0.750")	4.082"	4.460"	1.000"	1.750"	1.750"
80DB13-IDLER	13	No. 80 (1.000")	4.138"	4.660"	1.000"	2.250"	2.250"
100DB11-IDLER	11	No. 100 (1.250")	4.377"	5.010"	1.500"	2.875"	2.875"
35B13-IDLER	13	No. 35 (0.375")	1.567"	1.750"	0.500"	0.168"	0.750"
40B19-IDLER	19	No. 40 (0.500")	3.038"	3.280"	1.000"	0.284"	1.000"
50B17-IDLER	17	No. 50 (0.625")	3.401"	3.720"	1.000"	0.343"	1.000"
40A17-IDLER	17	No. 40 (0.500")	2.721"	2.960"	0.625"	0.720"	0.720"
50A15-IDLER	15	No. 50 (0.625")	3.006"	3.320"	0.625"	0.720"	0.720"
60A13-IDLER	13	No. 60 (0.750")	3.134"	3.490"	0.625"	0.720"	0.720"
80A12-IDLER	12	No. 80 (1.000")	3.864"	4.330"	0.750"	0.610"	0.610"



Whether you need a custom part made from heat treated steel or you need your custom part with its teeth hardened, the B&B Manufacturing Custom Shop can meet your custom requirements.