

AT10 TIMING PULLEYS

METRIC TIMING PULLEY

10 mm Pitch

For 32 mm Wide Belts





Hub

Zinc Plated Steel Flanges

Aluminum



Part Number	No. of Teeth	Type	Pitch Dia. (mm)	Out. Dia. (mm)	Flange Dia. (mm)	Bore (mm)	Face Width (mm)	Overall Length (mm)	Hub Dia. (mm)
47AT10/18-2	18	6F	57.3	55.5	60.0	10.0	38.0	47.0	40.0
47AT10/20-2	20	6F	63.7	61.8	66.0	12.0	38.0	47.0	46.0
47AT10/22-2	22	6F	70.0	68.2	66.0	12.0	38.0	47.0	50.0
47AT10/24-2	24	6F	76.4	74.6	83.0	12.0	38.0	47.0	58.0
47AT10/25-2	25	6F	79.6	77.8	83.0	12.0	38.0	47.0	60.0
47AT10/27-2	27	6F	86.0	84.1	91.0	12.0	38.0	47.0	60.0
47AT10/30-2	30	6F	95.5	93.7	97.0	12.0	38.0	47.0	60.0
47AT10/32-2	32	6F	101.9	100.0	106.0	12.0	38.0	47.0	65.0
47AT10/36-2	36	6F	114.6	112.8	119.0	16.0	38.0	47.0	70.0
47AT10/40-2	40	6F	127.3	125.5	131.0	16.0	38.0	47.0	80.0
47AT10/44-2	44	6F	140.1	138.2		16.0	38.0	47.0	90.0
47AT10/48-0	48	6	152.8	151.0	-	16.0	38.0	47.0	95.0
47AT10/60-0	60	6	191.0	189.1	-	16.0	38.0	47.0	110.0



For matching AT10 pitch belts, see page 213.

One of the many custom options that B&B Manufacturing can supply is custom bore drilling. If you don't see the bore size you are looking for, ask our experienced sales staff if we can customize an existing part or create a new part for you at your requested bore size.