

T5 TIMING PULLEYS

5 mm Pitch

For 25 mm Wide Belts

Hub



Zinc Plated Steel Flanges

Aluminum

METRIC TIMING PULLEY



Part Number	No. of Teeth	Type	Pitch Dia (mm)	Out. Dia. (mm)	Flange Dia (mm)	Bore (mm)	Face Width (mm)	Overall Length (mm)	Hub Dia. (mm)
36T5/10-2	10	6F	16.1	15.1	19.5	6.0	30.0	36.0	8.0
36T5/12-2	12	6F	19.3	18.3	23.0	6.0	30.0	36.0	12.0
36T5/14-2	14	6F	22.5	21.5	25.0	6.0	30.0	36.0	14.0
36T5/15-2	15	6F	24.1	23.1	28.0	6.0	30.0	36.0	16.0
36T5/16-2	16	6F	25.6	24.6	32.0	6.0	30.0	36.0	18.0
36T5/18-2	18	6F	28.8	27.8	32.0	6.0	30.0	36.0	20.0
36T5/19-2	19	6F	30.4	29.4	36.0	6.0	30.0	36.0	22.0
36T5/20-2	20	6F	31.0	31.0	36.0	6.0	30.0	36.0	24.0
36T5/22-2	22	6F	35.3	34.3	38.0	6.0	30.0	36.0	25.0
36T5/24-2	24	6F	38.4	37.4	42.0	6.0	30.0	36.0	26.0
36T5/25-2	25	6F	40.0	39.0	44.0	6.0	30.0	36.0	26.0
36T5/26-2	26	6F	41.6	40.6	44.0	6.0	30.0	36.0	26.0
36T5/27-2	27	6F	43.2	42.2	48.0	8.0	30.0	36.0	30.0
36T5/30-2	30	6F	48.0	47.0	51.0	8.0	30.0	36.0	34.0
36T5/32-2	32	6F	51.1	50.1	54.0	8.0	30.0	36.0	38.0
36T5/36-2	36	6F	57.5	56.5	63.0	8.0	30.0	36.0	38.0
36T5/40-2	40	6F	63.9	62.9	66.0	8.0	30.0	36.0	40.0
36T5/48-0	48	6	76.6	75.6	-	8.0	30.0	36.0	50.0
36T5/60-0	60	6	95.7	94.7	-	8.0	30.0	36.0	65.0



Using Lean Manufacturing and CONWIP production control systems, B&B Manufacturing strives to eliminate waste in costs, tooling and processes. B&B Manufacturing constantly monitors our processes in an effort to continuously improve our lead times, quality control, and costs. By combining Lean Manufacturing with a CONWIP (A hybrid push-pull kanban system) production control system, B&B Manufacturing is constantly improving upon our Just in Time production strategy to deliver precision mechanical components and Power Transmission parts to our clients when they need them.

B&B Manufacturing offers a free online service for locating and downloading CAD models in most CAD file formats.

Find this convenient engineering tool and others on our website at:

www.bbman.com.