

# AT10 TIMING PULLEYS

## METRIC TIMING PULLEY

10 mm Pitch

For 50 mm Wide Belts




Hub

Zinc Plated Steel Flanges

Aluminum



Part Number	No. of Teeth	Type	Pitch Dia (mm)	Out. Dia. (mm)	Flange Dia. (mm)	Bore (mm)	Face Width (mm)	Overall Length (mm)	Hub Dia. (mm)
66AT10/18-2	18	6F	57.3	55.5	60.0	10.0	57.0	66.0	40.0
66AT10/20-2	20	6F	63.7	61.8	66.0	12.0	57.0	66.0	46.0
66AT10/22-2	22	6F	70.0	68.2	66.0	12.0	57.0	66.0	50.0
66AT10/24-2	24	6F	76.4	74.6	83.0	12.0	57.0	66.0	58.0
66AT10/25-2	25	6F	79.6	77.8	83.0	12.0	57.0	66.0	60.0
66AT10/27-2	27	6F	86.0	84.1	91.0	12.0	57.0	66.0	60.0
66AT10/30-2	30	6F	95.5	93.7	97.0	12.0	57.0	66.0	60.0
66AT10/32-2	32	6F	101.9	100.0	106.0	12.0	57.0	66.0	65.0
66AT10/36-2	36	6F	114.6	112.8	119.0	16.0	57.0	66.0	70.0
66AT10/40-2	40	6F	127.3	125.5	131.0	16.0	57.0	66.0	80.0
66AT10/44-2	44	6F	140.1	138.2	-	16.0	57.0	66.0	90.0
66AT10/48-0	48	6	152.8	151.0	-	16.0	57.0	66.0	95.0
66AT10/60-0	60	6	191.0	189.1	-	16.0	57.0	66.0	110.0



For AT10 pitch pulley stock, see page 369.

At B&B Manufacturing, we have an extensive online catalog of off-the-shelf parts that meet a wide variety of needs in the power transmission and precision mechanical marketplaces.

But we know that sometimes it takes something special to do the job right. That's why we can modify any of our stock components to meet your unique performance and material specifications. We also offer fast, precision-engineered and quality manufactured components that can be built from the ground up in our custom shop.