


XL TIMING PULLEY BAR STOCK

0.200" / 5.08 mm Pitch
Steel



Timing Pulley Stock

Part Number	No. of Teeth	Metric		Inch		Shank Diameter	Shank Length	Minimum Usable Length	Overall Length
		Pitch Diameter	Outside Diameter	Pitch Diameter	Outside Diameter				
35XL-PS8S	35	56.6 mm	56.1 mm	2.228"	2.208"	0.750"	1.000"	8.000"	9.000"
36XL-PS8S	36	58.2 mm	57.7 mm	2.292"	2.272"	0.750"	1.000"	8.000"	9.000"
37XL-PS8S	37	59.8 mm	59.3 mm	2.355"	2.335"	0.750"	1.000"	8.000"	9.000"
38XL-PS8S	38	61.4 mm	60.9 mm	2.419"	2.399"	0.750"	1.000"	8.000"	9.000"
40XL-PS8S	40	64.7 mm	64.2 mm	2.546"	2.526"	0.750"	1.000"	8.000"	9.000"
42XL-PS8S	42	67.9 mm	67.4 mm	2.674"	2.654"	0.750"	1.000"	8.000"	9.000"
43XL-PS8S	43	69.5 mm	69.0 mm	2.737"	2.717"	0.750"	1.000"	8.000"	9.000"
44XL-PS8S	44	71.1 mm	70.6 mm	2.801"	2.781"	0.750"	1.000"	8.000"	9.000"
45XL-PS8S	45	72.8 mm	72.3 mm	2.865"	2.845"	0.750"	1.000"	8.000"	9.000"
46XL-PS8S	46	74.4 mm	73.9 mm	2.928"	2.908"	0.750"	1.000"	8.000"	9.000"
48XL-PS8S	48	77.6 mm	77.1 mm	3.056"	3.036"	0.750"	1.000"	8.000"	9.000"
50XL-PS8S	50	80.8 mm	80.3 mm	3.183"	3.163"	0.750"	1.000"	8.000"	9.000"
60XL-PS8S	60	97.0 mm	96.5 mm	3.820"	3.800"	0.750"	1.000"	8.000"	9.000"
62XL-PS8S	62	100.3 mm	99.7 mm	3.947"	3.927"	0.750"	1.000"	8.000"	9.000"
72XL-PS8S	72	116.4 mm	115.9 mm	4.584"	4.564"	1.000"	1.000"	8.000"	9.000"



At B&B Manufacturing, we have an extensive online catalog of off-the-shelf parts that meet a wide variety of needs in the power transmission and precision mechanical marketplaces.

But we know that sometimes it takes something special to do the job right. That's why we can modify any of our stock components to meet your unique performance and material specifications.

We also offer fast, precision-engineered and quality manufactured components that can be built from the ground up in our custom shop.