

AT5 TIMING PULLEYS

METRIC TIMING PULLEY

5 mm Pitch

For 25 mm Wide Belts



Hub

Zinc Plated Steel Flanges

Aluminum



Part Number	No. of Teeth	Type	Pitch Dia (mm)	Out. Dia. (mm)	Flange Dia (mm)	Bore (mm)	Face Width (mm)	Overall Length (mm)	Hub Dia. (mm)
38AT5/12-2	12	6F	19.1	17.9	23.0	-	32.0	38.0	12.0
38AT5/14-2	14	6F	22.3	21.1	25.0	-	32.0	38.0	14.0
38AT5/15-2	15	6F	23.9	22.7	28.0	6.0	32.0	38.0	16.0
38AT5/16-2	16	6F	25.5	24.2	32.0	6.0	32.0	38.0	18.0
38AT5/18-2	18	6F	28.7	27.4	32.0	6.0	32.0	38.0	20.0
38AT5/20-2	20	6F	31.8	30.6	36.0	6.0	32.0	38.0	24.0
38AT5/22-2	22	6F	35.0	33.9	38.0	6.0	32.0	38.0	25.0
38AT5/24-2	24	6F	38.2	37.0	42.0	8.0	32.0	38.0	26.0
38AT5/25-2	25	6F	39.8	38.6	44.0	8.0	32.0	38.0	26.0
38AT5/26-2	26	6F	41.4	40.2	44.0	8.0	32.0	38.0	26.0
38AT5/27-2	27	6F	43.0	41.8	48.0	8.0	32.0	38.0	30.0
38AT5/30-2	30	6F	47.8	46.6	51.0	8.0	32.0	38.0	34.0
38AT5/32-2	32	6F	50.9	49.7	54.0	8.0	32.0	38.0	38.0
38AT5/36-2	36	6F	57.3	56.1	63.0	8.0	32.0	38.0	38.0
38AT5/40-2	40	6F	63.7	62.5	66.0	8.0	32.0	38.0	40.0
38AT5/44-0	44	6	70.0	68.8	-	8.0	32.0	38.0	50.0
38AT5/48-0	48	6	76.4	75.2	-	8.0	32.0	38.0	50.0
38AT5/60-0	60	6	95.5	94.3	-	8.0	32.0	38.0	65.0
38AT5/72-0	72	6	114.6	113.4	-	10.0	32.0	38.0	80.0



For idler pulleys, see page 366.

Instead of doing the calculations and referencing dozens of pages of belt length tables (see pages 10-61), visit our website at www.bbman.com to take advantage of the convenience of our easy-to-use Belt Length Calculator. It is a free service designed to be a clear, accessible, and quick tool to choose a belt to fit your specifications.