


# AT10 TIMING PULLEY BAR STOCK

AT10 mm Pitch  
Aluminum

METRIC TIMING PULLEY STOCK



Timing Pulley Stock

| Part Number   | No. of Teeth | Metric         |                  | Inch           |                  | Shank Diameter | Shank Length | Minimum Usable Length | Overall Length |
|---------------|--------------|----------------|------------------|----------------|------------------|----------------|--------------|-----------------------|----------------|
|               |              | Pitch Diameter | Outside Diameter | Pitch Diameter | Outside Diameter |                |              |                       |                |
| 38AT10-PS160A | 38           | 120.9 mm       | 119.1 mm         | 4.760"         | 4.689"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |
| 40AT10-PS160A | 40           | 127.3 mm       | 125.5 mm         | 5.012"         | 4.939"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |
| 41AT10-PS160A | 41           | 130.4 mm       | 128.7 mm         | 5.134"         | 5.065"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |
| 42AT10-PS160A | 42           | 133.6 mm       | 131.9 mm         | 5.260"         | 5.191"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |
| 44AT10-PS160A | 44           | 140.0 mm       | 138.2 mm         | 5.512"         | 5.441"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |
| 45AT10-PS160A | 45           | 143.2 mm       | 141.4 mm         | 5.638"         | 5.567"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |
| 46AT10-PS160A | 46           | 146.4 mm       | 144.6 mm         | 5.764"         | 5.691"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |
| 48AT10-PS160A | 48           | 152.7 mm       | 151.0 mm         | 6.012"         | 5.943"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |
| 50AT10-PS160A | 50           | 159.1 mm       | 157.3 mm         | 6.264"         | 6.193"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |
| 51AT10-PS160A | 51           | 162.3 mm       | 160.5 mm         | 6.390"         | 6.319"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |
| 52AT10-PS160A | 52           | 165.5 mm       | 163.7 mm         | 6.516"         | 6.443"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |
| 54AT10-PS160A | 54           | 171.8 mm       | 170.1 mm         | 6.764"         | 6.695"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |
| 55AT10-PS160A | 55           | 175.0 mm       | 173.2 mm         | 6.890"         | 6.819"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |
| 56AT10-PS160A | 56           | 178.2 mm       | 176.4 mm         | 7.016"         | 6.945"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |
| 57AT10-PS160A | 57           | 181.4 mm       | 179.6 mm         | 7.142"         | 7.071"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |
| 58AT10-PS160A | 58           | 184.6 mm       | 182.8 mm         | 7.268"         | 7.195"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |
| 59AT10-PS160A | 59           | 187.7 mm       | 186.0 mm         | 7.390"         | 7.321"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |
| 60AT10-PS160A | 60           | 190.9 mm       | 189.1 mm         | 7.516"         | 7.445"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |
| 62AT10-PS160A | 62           | 197.3 mm       | 195.5 mm         | 7.768"         | 7.697"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |
| 70AT10-PS160A | 70           | 222.7 mm       | 221.0 mm         | 8.768"         | 8.699"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |
| 75AT10-PS160A | 75           | 238.7 mm       | 236.9 mm         | 9.398"         | 9.327"           | 1.000"         | 1.000"       | 6.300"                | 7.300"         |