


# H TIMING PULLEY BAR STOCK

0.500" Pitch

Aluminum



Timing Pulley Stock

Part Number	No. of Teeth	Metric		Inch		Shank Diameter	Shank Length	Minimum Usable Length	Overall Length
		Pitch Diameter	Outside Diameter	Pitch Diameter	Outside Diameter				
30H-PS10A	30	121.3 mm	119.9 mm	4.775"	4.721"	1.000"	1.000"	10.000"	11.000"
31H-PS10A	31	125.4 mm	124.0 mm	4.936"	4.882"	1.000"	1.000"	10.000"	11.000"
32H-PS10A	32	129.4 mm	128.0 mm	5.093"	5.039"	1.000"	1.000"	10.000"	11.000"
33H-PS10A	33	133.5 mm	132.1 mm	5.254"	5.200"	1.000"	1.000"	10.000"	11.000"
34H-PS10A	34	137.5 mm	136.1 mm	5.414"	5.360"	1.000"	1.000"	10.000"	11.000"
35H-PS10A	35	141.5 mm	140.2 mm	5.571"	5.519"	1.000"	1.000"	10.000"	11.000"
36H-PS10A	36	145.5 mm	144.2 mm	5.730"	5.676"	1.000"	1.000"	10.000"	11.000"
37H-PS10A	37	149.6 mm	148.3 mm	5.891"	5.837"	1.000"	1.000"	10.000"	11.000"
38H-PS10A	38	153.7 mm	152.3 mm	6.050"	5.996"	1.000"	1.000"	10.000"	11.000"
39H-PS10A	39	157.7 mm	156.4 mm	6.210"	6.156"	1.000"	1.000"	10.000"	11.000"
40H-PS10A	40	161.7 mm	160.3 mm	6.366"	6.312"	1.000"	1.000"	10.000"	11.000"



At B&B Manufacturing, we have an extensive online catalog of off-the-shelf parts that meet a wide variety of needs in the power transmission and precision mechanical marketplaces.

But we know that sometimes it takes something special to do the job right. That's why we can modify any of our stock components to meet your unique performance and material specifications. We also offer fast, precision-engineered and quality manufactured components that can be built from the ground up in our custom shop.