



MXL TIMING PULLEY BAR STOCK

0.080" / 2.03 mm Pitch
Aluminum




Part Number	No. of Teeth	Metric		Inch		Shank Diameter	Shank Length	Minimum Usable Length	Overall Length
		Pitch Diameter	Outside Diameter	Pitch Diameter	Outside Diameter				
80MP-PS8A	80	51.7 mm	51.2 mm	2.037"	2.017"	0.750"	0.750"	8.000"	8.750"
82MP-PS8A	82	53.0 mm	52.5 mm	2.088"	2.068"	0.750"	0.750"	8.000"	8.750"
84MP-PS8A	84	54.3 mm	53.8 mm	2.139"	2.119"	0.750"	0.750"	8.000"	8.750"
88MP-PS8A	88	56.9 mm	56.4 mm	2.241"	2.221"	0.750"	0.750"	8.000"	8.750"
90MP-PS8A	90	58.2 mm	57.7 mm	2.292"	2.272"	0.750"	0.750"	8.000"	8.750"
96MP-PS8A	96	62.1 mm	61.6 mm	2.445"	2.425"	0.750"	0.750"	8.000"	8.750"
98MP-PS8A	98	63.4 mm	62.9 mm	2.496"	2.476"	0.750"	0.750"	8.000"	8.750"
100MP-PS8A	100	64.7 mm	64.2 mm	2.546"	2.526"	0.750"	0.750"	8.000"	8.750"
102MP-PS8A	102	66.0 mm	65.5 mm	2.597"	2.577"	0.750"	0.750"	8.000"	8.750"
108MP-PS8A	108	69.9 mm	69.3 mm	2.750"	2.730"	0.750"	0.750"	8.000"	8.750"
110MP-PS8A	110	71.1 mm	70.6 mm	2.801"	2.781"	0.750"	0.750"	8.000"	8.750"
120MP-PS8A	120	77.6 mm	77.1 mm	3.056"	3.036"	0.750"	0.750"	8.000"	8.750"
130MP-PS8A	130	84.1 mm	83.6 mm	3.310"	3.290"	0.750"	0.750"	8.000"	8.750"
140MP-PS8A	140	90.6 mm	90.0 mm	3.565"	3.545"	0.750"	0.750"	8.000"	8.750"
150MP-PS8A	150	97.0 mm	96.5 mm	3.820"	3.800"	0.750"	0.750"	8.000"	8.750"
180MP-PS8A	180	118.2 mm	116.4 mm	4.654"	4.584"	0.750"	0.750"	8.000"	8.750"



For matching MXL pitch belts,
see page 180.



For MXL timing pulleys,
see page 2.



For idler pulleys,
see page 366.