

# POWERHOUSE™ TIMING PULLEYS

(Compatible with PowerGrip® GT2® and PowerGrip® GT3® pitches)

**8 mm Pitch**  
**For 12 mm Wide Belts**  
**Steel/Iron**  
**Black Oxide Plating**  
**Taper-Lock® Style**



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bushing	Face Width (in)	Overall Length (in)
22-8P12-1008	22	A1F	2.206	2.152	2.559	1008	0.875	0.875
23-8P12-1008	23	A1F	2.306	2.252	2.756	1008	0.875	0.875
24-8P12-1008	24	A1F	2.406	2.352	2.756	1008	0.875	0.875
25-8P12-1108	25	A1F	2.507	2.453	2.953	1108	0.875	0.875
26-8P12-1108	26	A1F	2.607	2.553	2.953	1108	0.875	0.875
27-8P12-1108	27	A1F	2.707	2.653	3.100	1108	0.875	0.875
28-8P12-1108	28	A1F	2.807	2.753	3.150	1108	0.875	0.875
29-8P12-1210	29	A1F	2.908	2.854	3.256	1210	1.000	1.000
30-8P12-1210	30	A1F	3.008	2.954	3.346	1210	1.000	1.000
31-8P12-1210	31	A1F	3.108	3.054	3.420	1210	1.000	1.000
32-8P12-1210	32	A1F	3.208	3.154	3.543	1210	1.000	1.000
33-8P12-1210	33	A1F	3.309	3.255	3.735	1210	1.000	1.000
34-8P12-1210	34	A1F	3.409	3.355	3.819	1210	1.000	1.000
35-8P12-1210	35	A1F	3.509	3.455	3.938	1210	1.000	1.000
36-8P12-1210	36	A1F	3.609	3.555	3.938	1210	1.000	1.000
37-8P12-1210	37	A1F	3.710	3.656	4.050	1210	1.000	1.000
38-8P12-1210	38	A1F	3.810	3.756	4.156	1210	1.000	1.000
40-8P12-1210	40	B1F	4.010	3.956	4.331	1210	0.750	1.000
44-8P12-1610	44	B1F	4.411	4.357	4.764	1610	0.750	1.000
48-8P12-1610	48	B1F	4.812	4.758	5.157	1610	0.750	1.000
56-8P12-1610	56	B1F	5.614	5.560	5.945	1610	0.750	1.000
60-8P12-1610	60	B1F	5.961	5.907	6.375	1610	0.750	1.000
64-8P12-1610	64	B1F	6.416	6.362	6.772	1610	0.750	1.000
72-8P12-1610	72	B1F	7.218	7.164	7.575	1610	0.750	1.000
80-8P12-1610	80	B1F	8.020	7.966	8.386	1610	0.750	1.000
90-8P12-1610	90	C2	9.023	8.969	-	1610	0.750	1.000

