







POWERHOUSE™ TIMING PULLEYS

(Compatible with PowerGrip® GT2® and PowerGrip® GT3® pitches)

8 mm Pitch
For 50 mm Wide Belts
Steel/Iron
Black Oxide Plating



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bore / Bushing	Face Width (in)	Overall Length (in)
28-8P50-6FS6	28	6F	2.807	2.753	3.150	0.500"	2.380	3.000
30-8P50-1210	30	A1F	3.008	2.954	3.346	1210	2.380	2.380
32-8P50-1210	32	A1F	3.208	3.154	3.543	1210	2.380	2.380
34-8P50-1610	34	A1F	3.409	3.355	3.819	1610	2.380	2.380
36-8P50-1610	36	A1F	3.609	3.555	3.938	1610	2.380	2.380
38-8P50-1610	38	A1F	3.810	3.756	4.156	1610	2.380	2.380
40-8P50-2012	40	A1F	4.010	3.956	4.331	2012	2.380	2.380
44-8P50-2012	44	A1F	4.411	4.357	4.764	2012	2.380	2.380
48-8P50-2012	48	A1F	4.812	4.758	5.157	2012	2.380	2.380
56-8P50-2517	56	A1F	5.614	5.560	5.945	2517	2.380	2.380
64-8P50-2517	64	A1F	6.416	6.362	6.772	2517	2.380	2.380
72-8P50-2517	72	A1F	7.218	7.164	7.575	2517	2.380	2.380
80-8P50-2517	80	A1F	8.020	7.966	8.386	2517	2.380	2.380
90-8P50-3020	90	A1	9.023	8.969	-	3020	2.380	2.380
112-8P50-3020	112	A2	11.229	11.175	-	3020	2.380	2.380
144-8P50-3020	144	A3	14.437	14.383	-	3020	2.380	2.380
192-8P50-3020	192	A3	19.249	19.195	-	3020	2.380	2.380



For matching 8 mm POWERHOUSE™ pitch belts, see page 240.