


AKH V-BELT SHEAVES

For 4L, 3L, or A Belts
Single Groove
0.750" Face Width
Cast Iron
Split Taper Style
H Bushing




Part Number	Diameters			Type	Dimensions							Wt. Ea. (Lbs.)
	Out. Dia. (in)	Pitch Dia. "A"	Pitch Dia. "3L"		OAL	L	P	C	X	G	E	
AK30H	3.050	2.800	2.46	1	1.813	1.250	0.875	-	1.188	0.438	0.188	1.1
AK32H	3.250	3.000	2.66	1	1.813	1.250	0.875	-	1.188	0.438	0.188	1.2
AK34H	3.450	3.200	2.86	2	1.500	1.250	0.563	-	0.875	0.438	0.188	1.0
AK39H	3.750	3.500	3.16	2	1.500	1.250	0.563	-	0.875	0.438	0.188	1.4
AK41H	3.950	3.700	3.36	2	1.500	1.250	0.563	-	0.875	0.438	0.188	1.6
AK44H	4.250	4.000	3.66	2	1.500	1.250	0.563	-	0.875	0.438	0.188	1.9
AK46H	4.450	4.200	3.86	2	1.500	1.250	0.563	-	0.875	0.438	0.188	1.9
AK49H	4.750	4.500	4.16	2	1.500	1.250	0.563	-	0.875	0.438	0.188	2.1
AK51H	4.950	4.700	4.36	2	1.500	1.250	0.563	-	0.875	0.438	0.188	2.3
AK54H	5.250	5.000	4.66	2	1.500	1.250	0.563	-	0.875	0.438	0.188	2.0
AK56H	5.450	5.200	4.86	2	1.500	1.250	0.563	-	0.875	0.438	0.188	2.3
AK59H	5.750	5.500	5.16	2	1.500	1.250	0.563	-	0.875	0.438	0.188	2.4
AK61H	5.950	5.700	5.36	3	1.500	1.250	0.563	0	0.875	0.438	0.188	2.5
AK64H	6.250	6.000	5.66	3	1.500	1.250	0.563	0	0.875	0.438	0.188	2.7
AK66H	6.450	6.200	5.86	3	1.500	1.250	0.563	0	0.875	0.438	0.188	2.8
AK69H	6.750	6.500	6.16	3	1.500	1.250	0.563	0	0.875	0.438	0.188	3.2
AK71H	6.950	6.700	6.36	3	1.500	1.250	0.563	0	0.875	0.438	0.188	3.1
AK74H	7.250	7.000	6.66	3	1.500	1.250	0.563	0	0.875	0.438	0.188	3.3
AK79H	7.750	7.500	7.16	3	1.500	1.250	0.563	0	0.875	0.438	0.188	3.5
AK84H	8.250	8.000	7.66	3	1.500	1.250	0.563	0	0.875	0.438	0.188	3.6
AK89H	8.750	8.500	8.16	3	1.500	1.250	0.563	0	0.875	0.438	0.188	4.0
AK94H	9.250	9.000	8.66	3	1.500	1.250	0.563	0	0.875	0.438	0.188	4.4
AK99H	9.750	9.500	9.16	3	1.500	1.250	0.563	0	0.875	0.438	0.188	4.7
AK104H	10.250	10.000	9.66	3	1.500	1.250	0.563	0	0.875	0.438	0.188	4.5
AK109H	10.750	10.500	10.16	3	1.500	1.250	0.563	0	0.875	0.438	0.188	5.1
AK114H	11.250	11.000	10.66	3	1.500	1.250	0.563	0	0.875	0.438	0.188	5.5
AK124H	12.250	12.000	11.66	3	1.500	1.250	0.563	0	0.875	0.438	0.188	6.1
AK134H	13.250	13.000	12.66	3	1.500	1.250	0.563	0	0.875	0.438	0.188	7.4
AK144H	14.250	14.000	13.66	3	1.500	1.250	0.563	0	0.875	0.438	0.188	7.8
AK154H	15.250	15.000	14.66	3	1.500	1.250	0.563	0	0.875	0.438	0.188	8.8
AK184H	18.250	18.000	17.66	3	1.500	1.250	0.563	0	0.875	0.438	0.188	11.3

TYPE 1



TYPE 2



TYPE 3

