

3V V-BELT SHEAVES

For 3V V-Belts

4 Grooves

1.906" Face Width


Cast Iron

QD® Style




Part Number	Type	Pitch Dia. "3V" Belts (in)	Out. Dia. (in)	Bushing	Bore Range	E	L	M	Wt. Ea. (Lbs.)
43V265JA	D1	2.60	2.65	JA	0.500" - 1.250"	0.375	1.000	1.281	1.3
43V280JA	D1	2.75	2.80	JA	0.500" - 1.250"	0.375	1.000	1.281	1.7
43V300SH	E1	2.95	3.00	SH	0.500" - 1.625"	1.500	1.313	0.906	2.0
43V315SH	E1	3.10	3.15	SH	0.500" - 1.625"	1.500	1.313	0.906	2.2
43V335SH	D1	3.30	3.35	SH	0.500" - 1.625"	0.531	1.313	1.125	2.3
43V365SH	D1	3.60	3.65	SH	0.500" - 1.625"	0.531	1.313	1.125	2.8
43V412SH	A1	4.07	4.12	SH	0.500" - 1.625"	0.156	1.313	0.438	3.4
43V450SDS	A1	4.45	4.50	SDS	0.500" - 2.000"	0.156	1.313	0.438	4.0
43V475SDS	A1	4.70	4.75	SDS	0.500" - 2.000"	0.156	1.313	0.438	4.6
43V500SDS	A1	4.95	5.00	SDS	0.500" - 2.000"	0.156	1.313	0.438	5.2
43V530SDS	A1	5.25	5.30	SDS	0.500" - 2.000"	0.156	1.313	0.438	5.8
43V560SDS	A1	5.55	5.60	SDS	0.500" - 2.000"	0.156	1.313	0.438	6.8
43V600SK	D1	5.95	6.00	SK	0.500" - 2.625"	0.156	1.938	0.125	8.3
43V650SK	D1	6.45	6.50	SK	0.500" - 2.625"	0.156	1.938	0.125	10.0
43V690SK	D1	6.85	6.90	SK	0.500" - 2.625"	0.156	1.938	0.125	11.9
43V800SK	D2	7.95	8.00	SK	0.500" - 2.625"	0.156	1.938	0.125	13.0
43V1060SK	D3	10.55	10.60	SK	0.500" - 2.625"	0.156	1.938	0.125	16.5
43V1400SK	D3	13.95	14.00	SK	0.500" - 2.625"	0.156	1.938	0.125	22.5
43V1900SF	D3	18.95	19.00	SF	0.500" - 2.938"	0.219	2.063	0.063	35.0
43V2500SF	D3	24.95	25.00	SF	0.500" - 2.938"	0.219	2.063	0.063	57.0
43V3350E	C3	33.45	33.50	E	0.875" - 3.500"	0.656	2.750	0.188	84.0


TYPE A



TYPE C



TYPE D



TYPE E

