

# POWERHOUSE™ HTD®

## TIMING PULLEYS

8 mm Pitch

For 20 mm Wide Belts

Steel/Iron

Black Oxide Plating



Part Number	No. of Teeth	Type	Pitch Dia. (in)	Out. Dia. (in)	Flange Dia. (in)	Bore / Bushing	Face Width (in)	Overall Length (in)	Hub Dia. (in)
22-8M20-6FS6	22	6F	2.206	2.152	2.559	0.500"	1.125	1.125	1.625
QD24-8M-20	24	E1F	2.406	2.352	2.756	JA	1.125	1.125	-
QD26-8M-20	26	E1F	2.607	2.553	2.953	JA	1.125	1.125	-
QD28-8M-20	28	3F	2.807	2.759	3.150	H	1.125	1.125	-
QD30-8M-20	30	E1F	3.008	2.958	3.346	H	1.125	1.125	-
QD32-8M-20	32	C1F	3.208	3.156	3.543	SH	1.125	1.125	-
QD34-8M-20	34	D1F	3.409	3.355	3.819	SH	1.125	1.125	-
QD36-8M-20	36	D1F	3.609	3.555	3.937	SH	1.125	1.125	-
QD38-8M-20	38	3F	3.810	3.756	4.134	SH	1.125	1.125	-
QD40-8M-20	40	D1F	4.010	3.956	4.331	SH	1.125	1.125	-
QD44-8M-20	44	C1F	4.411	4.357	4.764	SDS	1.125	1.125	-
QD48-8M-20	48	C1F	4.812	4.758	5.157	SDS	1.125	1.125	-
QD56-8M-20	56	C1F	5.614	5.560	5.945	SDS	1.125	1.125	-
QD64-8M-20	64	C1F	6.416	6.362	6.772	SDS	1.125	1.125	-
QD72-8M-20	72	C2F	7.218	7.164	7.598	SDS	1.125	1.125	-
QD80-8M-20	80	C2F	8.020	7.966	8.386	SDS	1.125	1.125	-
QD90-8M-20	90	D2	9.023	8.969	-	SDS	1.125	1.125	-
QD112-8M-20	112	C3	11.229	11.175	-	SK	1.125	1.125	-

