


AT5 TIMING PULLEY BAR STOCK

AT5 mm Pitch
Aluminum

METRIC TIMING PULLEY STOCK



Timing Pulley Stock

Part Number	No. of Teeth	Metric		Inch		Shank Diameter	Shank Length	Minimum Usable Length	Overall Length
		Pitch Diameter	Outside Diameter	Pitch Diameter	Outside Diameter				
35AT5-PS160A	35	55.7 mm	54.5 mm	2.193"	2.144"	0.750"	0.800"	6.300"	7.100"
36AT5-PS160A	36	57.3 mm	56.1 mm	2.255"	2.207"	0.750"	0.800"	6.300"	7.100"
38AT5-PS160A	38	60.5 mm	59.3 mm	2.381"	2.333"	0.750"	0.800"	6.300"	7.100"
40AT5-PS160A	40	63.7 mm	62.5 mm	2.506"	2.459"	0.750"	0.800"	6.300"	7.100"
42AT5-PS160A	42	66.8 mm	65.6 mm	2.630"	2.583"	0.750"	0.800"	6.300"	7.100"
44AT5-PS160A	44	70.0 mm	68.8 mm	2.756"	2.709"	0.750"	0.800"	6.300"	7.100"
45AT5-PS160A	45	71.6 mm	70.4 mm	2.819"	2.772"	0.750"	0.800"	6.300"	7.100"
46AT5-PS160A	46	73.2 mm	72.0 mm	2.882"	2.835"	0.750"	0.800"	6.300"	7.100"
48AT5-PS160A	48	76.3 mm	75.2 mm	3.004"	2.959"	0.750"	0.800"	6.300"	7.100"
50AT5-PS160A	50	79.5 mm	78.4 mm	3.130"	3.085"	1.000"	1.000"	6.300"	7.300"
52AT5-PS160A	52	82.7 mm	81.6 mm	3.256"	3.211"	1.000"	1.000"	6.300"	7.300"
54AT5-PS160A	54	85.9 mm	84.7 mm	3.382"	3.335"	1.000"	1.000"	6.300"	7.300"
55AT5-PS106A	55	87.5 mm	86.3 mm	3.445"	3.398"	1.000"	1.000"	6.300"	7.300"
56AT5-PS160A	56	89.1 mm	87.9 mm	3.508"	3.461"	1.000"	1.000"	6.300"	7.300"
58AT5-PS160A	58	92.3 mm	91.1 mm	3.634"	3.587"	1.000"	1.000"	6.300"	7.300"
60AT5-PS160A	60	95.4 mm	94.3 mm	3.756"	3.711"	1.000"	1.000"	6.300"	7.300"
62AT5-PS160A	62	98.6 mm	97.5 mm	3.882"	3.837"	1.000"	1.000"	6.300"	7.300"
64AT5-PS160A	64	101.8 mm	100.7 mm	4.008"	3.963"	1.000"	1.000"	6.300"	7.300"
65AT5-PS160A	65	103.5 mm	102.3 mm	4.073"	4.026"	1.000"	1.000"	6.300"	7.300"
70AT5-PS160A	70	111.4 mm	110.2 mm	4.386"	4.339"	1.000"	1.000"	6.300"	7.300"
72AT5-PS160A	72	114.5 mm	113.4 mm	4.508"	4.463"	1.000"	1.000"	6.300"	7.300"