

# POWERHOUSE™ HTD®

## TIMING PULLEYS

8 mm Pitch

For 85 mm Wide Belts





Iron

Black Oxide Plating

QD® Style



Part Number	No. of Teeth	Type	Pitch Dia	Out. Dia	Flange Dia.	Bore	Face Width	Overall Length
QD34-8M-85	34	A1F	3.409	3.355	3.819	SH	3.75	3.75
QD36-8M-85	36	A1F	3.609	3.555	3.937	SH	3.75	3.75
QD38-8M-85	38	A1F	3.81	3.756	4.134	SH	3.75	3.75
QD40-8M-85	40	A1F	4.01	3.956	4.331	SD	3.75	3.75
QD44-8M-85	44	A1F	4.411	4.357	4.764	SD	3.75	3.75
QD48-8M-85	48	A1F	4.812	4.758	5.157	SD	3.75	3.75
QD56-8M-85	56	A1F	5.614	5.56	5.945	SK	3.75	3.75
QD64-8M-85	64	A1F	6.416	6.362	6.772	SK	3.75	3.75
QD72-8M-85	72	A1F	7.218	7.164	7.598	SF	3.75	3.75
QD80-8M-85	80	A1F	8.02	7.966	8.386	SF	3.75	3.75
QD90-8M-85	90	A2	9.023	8.969	-	SF	3.75	3.75
QD112-8M-85	112	A3	11.229	11.175	-	SF	3.75	3.75
QD144-8M-85	144	A3	14.437	14.383	-	E	3.75	3.75
QD192-8M-85	192	A3	19.249	19.195	-	E	3.75	3.75



B&B Manufacturing has invested in a new Low Temperature Black Oxide line from Birchwood Casey. This system brings a previously outsourced process into B&B Manufacturing allowing us a cost-effective solution with a quicker turn around time. This particular system named TRU TEMP® provides a finish without Salt Bleed Out on all non-Stainless Steels and Cast Iron while remaining safe, operator friendly, RoHS compliant, and with no EPA problems.